


■ガス管用タップ



- テーパー (PT)
- ストレート (PS)
- ストレート (PF) (角度55°)

呼び寸法	外径の 基本寸法	全 長	刃 長	シャンク 外 径	SKS		SKH		SKS 左ねじ		SKH 左ねじ
1/16-28	7.723	54 ^{mm}	18 ^{mm}	8 ^{mm}							
1/8-28	9.728	55	19	8							
1/4-19	13.157	62	28	11							
3/8-19	16.662	65	28	14							
1/2-14	20.955	80	35	18							
5/8-14	22.912	85	35	20							
3/4-14	26.441	85	35	23							
7/8-14	30.202	90	40	24							
1-11	33.249	95	45	26							
1 1/8-11	37.898	105	45	30							
1 1/4-11	41.910	105	45	32							
1 3/8-11	44.325	110	45	35							
1 1/2-11	47.803	110	45	38							
1 3/4-11	53.748	115	45	40							
2-11	59.614	120	50	46							
2 1/4-11	65.712	130	55	50							
2 1/2-11	75.814	145	65	55							
2 3/4-11	81.537	150	65	60							
3-11	87.884	155	65	65							
3 1/2-11	100.330	165	68	70							
4-11	113.030	170	70	75							

■ガス管用タップ (アメリカねじ)

- テーパー (NPT)・ストレート (NPS) (角度60°)

呼び寸法	外径の 基本寸法	全 長	刃 長	SKS		SKH
1/16-27	7,769 ^{mm}	54 ^{mm}	17.5 ^{mm}			
1/8-27	10,116	54	19.1			
1/4-18	13,427	61.9	27.0			
3/8-18	16,866	65.1	27.0			
1/2-14	20,980	79.4	34.9			
5/8-14						
3/4-14	26,326	82.6	34.9			
7/8-14						
1-11 1/2	32,932	95.3	44.5			
1 1/8-11 1/2						
1 1/4-11 1/2	41,689	101.6	44.5			
1 1/2-11 1/2	47,758	108	44.5			
1 3/4-11 1/2						
2-11 1/2	59,796	114.3	44.5			
2 1/4-8						
2 1/2-8	72,273	139.7	65.1			
3-8	88,182	152.4	66.7			