
 Machine Bolt Dia. **42mm** Models with the best balance between strength and lightness.

**No. GT-4200PF**

**25.4** Pin-lock

**4** Adjust dial




 Machine Bolt Dia. **52mm** Models with the best balance between strength and lightness.

**No. GT-S55R**

**25.4** Pin-lock

**4** Adjust dial

Noise reducer



Model No.	Capacity Ordinary Bolt Dia. (mm)	Torque Range (N·m)	Max. Torque (N·m)	No Load Speed (rpm)	Air Consumption (ml/min)	Hose Coupling	Air Hose Inner Dia. (mm)	Overall Length (mm)	Weight (kg)	Accessories		EDP No.
										Plug	L-wrench	
<b>GT-4200PF</b>	42	343~1863	2250	2,500	1.0	Rc 3/8	12.7	297	11.5	BPB-3	H6	335388
<b>GT-S55R</b>	52	343~2450	3000	2,800	1.2	Rc 1/2	12.7	610	17.0	1/2"×1/2" (hose nipple)	H6	335391

\*Air pressure: 0.6MPa \*Overall length and Weight: Accessories not included. \*Capacity is listed as instant reference and depends on operation conditions.

## One point

Grip shape specialized for working with tires

Designed so that the center of gravity comes to the center of the whole body with the socket and air hose attached.

Very recommended to large tire shops replacing many tires a day.



**No. GT-3800LX**

