


SELOS · KNIFE EDGE DISCONNECT AND FUSE BLOCKS WITH SCREW CONNECTION

WT 2,5 TKM...

- Knife edge disconnect block for mounting on TS 35
- Nominal cross section 2,5 mm²
- Connection capacity: 2 wires, equal size 0,14 – 1,5 mm²



Description	Type	Part No.	Std. Pack
Knife edge disconnect block	gray WT 2,5 TKM	58.503.2055.0	100
Knife edge disconnect block with 2 test bolts	blue WT 2,5 TKM BL gray WT 2,5 TKM P	58.503.2055.6 58.503.2355.0	100 100
Feed-through block, identically-shaped	gray WT 2,5 TKM D	58.503.2155.0	100
Feed-through block, identically-shaped	blue WT 2,5 TKM D BL	58.503.2155.6	100


GENERAL DATA	
Width / length / height, incl. TS 7.5	5 mm / 56 mm / 50 mm
Wire strip length	9 mm
Approvals	☐

TECHNICAL DATA		IEC	
Cross section fine-stranded		0.14 – 4 mm ²	
Cross section solid/stranded		0.14 – 4 mm ²	
Cross section, AWG			
Rated current		20 A	
Rated voltage		500 V	
Rated impulse voltage		6 kV	
Pollution degree		3	

ACCESSORIES		Type	Part No.	Std. Pack
End plate		AP WT 4 D1/2	07.313.2955.0	10
Partition		TW WT 4 E	07.313.2855.0	10
Cross connector	2-pole	IVB WKF 2,5-2	Z7.280.6227.0	10
	5-pole	IVB WKF 2,5-5	Z7.280.6527.0	10
	10-pole	IVB WKF 2,5-10	Z7.280.7027.0	10
	20-pole	IVB WKF 2,5-20	Z7.280.8027.0	10

WT 4 TKM...

- Knife edge disconnect block for mounting on TS 35
- Nominal cross section 4 mm²
- Connection capacity: 2 wires, equal size 0,14 – 2,5 mm²



Description	Type	Part No.	Std. Pack
Knife edge disconnect block	gray WT 4 TKM	58.504.2055.0	100
Knife edge disconnect block with 2 test bolts	blue WT 4 TKM BL gray WT 4 TKM P	58.504.2055.6 58.504.2355.0	100 100

GENERAL DATA	
Width / length / height, incl. TS 7.5	6 mm / 56 mm / 50 mm
Wire strip length	9 mm
Approvals	☐ VDE ☐ CE ☐

TECHNICAL DATA		IEC		UL	CSA
Cross section fine-stranded		0.14 – 6 mm ²			
Cross section solid/stranded		0.14 – 6 mm ²			
Cross section, AWG				26 – 10	26 – 10
Rated current				24 A	16 A
Rated voltage				500 V	300 V
Rated impulse voltage				6 kV	300 V
Pollution degree				3	


ACCESSORIES		Type	Part No.	Std. Pack
End plate		AP WT 4 D1/2	07.313.2955.0	10
Partition		TW WT 4 E	07.313.2855.0	10
Cross connector	2-pole	IVB WKF 4-2	Z7.261.1227.0	10
	5-pole	IVB WKF 4-5	Z7.261.1527.0	10
	10-pole	IVB WKF 4-10	Z7.261.2027.0	10

WT 4 FSI

- Fuse block for automobile fuses (mini) for mounting on TS 35
- Nominal cross section 4 mm²
- Connection capacity: 2 wires, equal size 0,14 – 2,5 mm²

¹⁾ Observe the derating curve, available in our e-catalog at <https://eshop.wieland-electric.com>

²⁾ determined by the fuse inserted



Description	Type	Part No.	Std. Pack
Fuse block	gray WT 4 FSI	58.504.4155.0	100

GENERAL DATA	
Width / length / height, incl. TS 7.5	6 mm / 56 mm / 50 mm
Wire strip length	9 mm
Approvals	

TECHNICAL DATA		IEC	
Cross section fine-stranded		0.14 – 6 mm ²	
Cross section solid/stranded		0.14 – 6 mm ²	
Cross section, AWG			
Rated current		max. 20 A ¹⁾	
Rated voltage		²⁾	
Rated impulse voltage		6 kV	
Pollution degree		3	

ACCESSORIES		Type	Part No.	Std. Pack
End plate		AP WT 4 D1/2	07.313.2955.0	10
Partition		TW WT 4 E	07.313.2855.0	10
Cross connector	2-pole	IVB WKF 4-2	Z7.261.1227.0	10
	5-pole	IVB WKF 4-5	Z7.261.1527.0	10
	10-pole	IVB WKF 4-10	Z7.261.2027.0	10