


WSP Type

Examples of model number formation

2	WSP	6	-S	300	CM	H	/A
1	2	3	4	5	6	7	8

- 1** Q'ty of Nut **2** Part No. **3** Spline-shaft diameter
4 S:Solid, H:Hollow **5** Spline-shaft overall length
6 Preload : CT(Tight), CM(Middle), CL(Loose)
7 Accuracy symbol-Nomal(No symbol), High(H), Precision(P)
8 SUJ2(No symbol), Stainless steel(/A)

* When the grease nipple is necessary, please ask WON.



Part No.	Main dimensions											
	Outer Diameter D	Allowable Tolerance	L ₁	L ₂	W	Allowable Tolerance	t	ℓ	d	Allowable Tolerance	Length L	Max. length
WSP 4 ⁽²⁾	8	0	12	7.9	-	-	1	-	4		100 150	200
WSP 5	10	-0.009	18	8.9	2		1.2	6	5	0 -0.012	100 150	200
WSP 6	12	0	21	12.4	2		1.2	6	6		150 200	300
WSP 8	15	-0.011	25	14.6	2.5	+0.014 0	1.5	8.5	8	0	150 200 250	500
WSP 10	19		30	18.2	3		1.8	11	10	-0.015	200 300	600
WSP 12	21	0 -0.013	35	23	3		1.8	15	12	0	200 300 400	800
WSP 15	23		40	27	3.5		2	20	13.6	-0.018	200 300 400	1000
WSP 20	30		50	33	4	+0.018 0	2.5	26	18.2		300 400 500 600	1000
WSP 25	37	0 -0.016	60	39.2	5		3	29	22.6	0 -0.021	300 400 500 600 800	
WSP 30	45		70	43	7		4	35	27.2		400 500 600	1200
WSP 40	60	0 -0.019	100	70.8	10	+0.022 0	4.5	55	37.2	0 -0.025	700 1100	

Note(1) As for the Static load rating moment T_M , the upside figures are for the value for one nut and the downside figure are for the values for 2 nuts to be closely adhered.

(2) There are no seals in WSP 4.