

IMPACT WRENCH COMPOSITE

Bolt Capacity 10mm [STRAIGHT TYPE]

- Smallest palm-size. • Butterfly lever. • 360 degree Swivel inlet.

SP-1850

3/8" Retainer ring

4 Regulator dial



Bolt Capacity 10mm [STRAIGHT TYPE]

- Lightweight and compact. • Butterfly lever for Right/Left rotation switching. • 360 degree swivel inlet.

SP-1138

3/8" Retainer ring

4 Regulator dial



Bolt Capacity 10mm

- Lightweight and compact. • Reverse button. • Variable speed trigger.

SP-1135B

3/8" Retainer ring

F Stepless regulator dial



Bolt Capacity 16mm

- Reverse button. • Variable speed trigger.

SP-1140EX

1/2" Retainer ring

4 Regulator lever



Option
• #02413811 Protect cover

Bolt Capacity 16mm [LIGHTWEIGHT TYPE]

- Lightweight. • Reversible lever. • Variable speed trigger. • With protective cover

SP-1143

1/2" Retainer ring

4 Regulator lever



Bolt Capacity 14mm [LIGHTWEIGHT TYPE]

- Compact body. • Reverse button. • Variable speed trigger. • Built-in power regulator.

SP-1143S

3/8" Retainer ring

4 Regulator lever



EDP	Model No.	Sq. Drive (inch)	Hammer	Torque Range (N·m)	Free Speed (min ⁻¹)	Overall Length (mm)	Air Consumption (ml/min)	Hose Coupling	Net Weight (kg)	JAN (4545695)
370025	SP-1850	3/8"	Double Hammer	5~50	10000	137	0.2	3/8"NPT	0.5	001353
370035	SP-1138	3/8"	Single Hammer	7~90	12500	180	0.3	3/8"NPT	0.9	001278
370038	SP-1135B	3/8"	Single Hammer	7~90	12000	138	0.3	3/8"NPT	1.3	000103
370033	SP-1140EX	1/2"	Twin dog clutch	50~500	6000	185	0.6	1/4"NPT	2.6	000189
370023	SP-1143	1/2"	Dyna Jaw clutch	50~320	8000	163	0.4	1/4"NPT	1.6	000196
370181	SP-1143S	3/8"	Dyna Jaw clutch	50~320	8000	163	0.4	3/8"NPT	1.6	002114

Air pressure: 0.62 MPa Air hose inner dia.: 9.5 mm Rear exhaust Air connector included