


WSPL Type

Examples of model number formation

2 WSPL 6 - S 300 CM H /A
1 2 3 4 5 6 7 8

- 1** Q'ty of Nut **2** Part No. **3** Spline-shaft diameter
- 4** S:Solid, H:Hollow **5** Spline-shaft overall length
- 6** Preload : CT(Tight), CM(Middle), CL(Loose)
- 7** Accuracy symbol-Nomal(No symbol), High(H), Precision(P)
- 8** SUJ2(No symbol), Stainless steel(/A)

* When the grease nipple is necessary, please ask WON.



Part No.	Main dimensions											
	Outer Diameter D	Allowable Tolerance	L ₁	L ₂	W	Allowable Tolerance	t	ℓ	d	Allowable Tolerance	Length L	Max. length
WSPL 5	10	0 -0.009	26	17.4	2	+0.014 0	1.2	6	5	0 -0.012	100 150	200
WSPL 6	12	0	30	21.4	2		1.2	8	6		150 200	300
WSPL 8	15	-0.011	37	26.6	2.5		1.5	8.5	8		150 200 250	500
WSPL 10	19	0 -0.013	47	34.9	3		1.8	11	10	0	200 300	600
WSPL 12	21		54	42	3	1.8	15	12	-0.015	200 300 400	800	
WSPL 15	23	0 -0.016	65	52	3.5	+0.018 0	2	20	13.6	0	200 300 400	1000
WSPL 20	30		71	54	4		2.5	26	18.2	-0.018	300 400 500 600	1000
WSPL 25	37	0 -0.021	84	63.2	5	+0.022 0	3	29	22.6	0	300 400 500 600 800	1200
WSPL 30	45		98	71	7		4	35	27.2	-0.021	400 500 600 700 1100	

Note(1) As for the Static load rating moment T_M , the upside figures are for the value for one nut and the downside figure are for the values for 2 nuts to be closely adhered.