


WSPTF Type

Examples of model number formation

2 WSPTF 6-S 300 CM H /A
1 2 3 4 5 6 7 8

- 1** Q'ty of Nut **2** Part No. **3** Spline-shaft diameter
- 4** S:Solid, H:Hollow **5** Spline-shaft overall length
- 6** Preload : CT(Tight), CM(Middle), CL(Loose)
- 7** Accuracy symbol-Nomal(No symbol), High(H), Precision(P)
- 8** SUJ2(No symbol), Stainless steel(/A)

* When the grease nipple is necessary, please ask WON.



Part No.	Main dimensions										
	Outer Diameter D	Allowable Tolerance	L ₁	D ₂	T	pcd	X x Y x Z	d	Allowable Tolerance	Length L	Max. length
WSPTF 6	14	0 -0.011	25	30	5	22	3.4 x 6.5 x 3.3	6		150 200	300
WSPTF 8	16	0	25	32	5	24	3.4 x 6.5 x 3.3	8	0 -0.012	150 200 250	500
WSPTF 10	21	-0.013	33	42	6	32	4.5 x 8 x 4.4	10		200 300	600
WSPTF 12	24		36	44	7	33	4.5 x 8 x 4.4	12	0	200 300 400	800
WSPTF 15	31	0 -0.016	50	51	7	40	4.5 x 8 x 4.4	13.6	-0.015	200 300 400	1000
WSPTF 20	35		63	58	9	45	5.5 x 9.5 x 5.4	18.2	0 -0.018	300 400 500 600	1000

Note(1) As for the Static load rating moment T_M , the upside figures are for the value for one nut and the downside figure are for the values for 2 nuts to be closely adhered.