



R (for Corner castors)

● Tire	SBR
● Wheel center	-
● Bearing	-
● Operating temp.	-40°C~+80°C
● Hardness	(HS) 70-75
● Characteristics	High elasticity. Wearing resistance.
● Applicable to Castors on	P.47



R-50CC	50	20	23	6	-	30 (290)
R-65CC	65	25	30	8	-	40 (390)
R-75CC	75	25	30	8	-	50 (490)

R (for Shock absorbing castors)

● Tire	SBR
● Wheel center	-
● Bearing	-
● Operating temp.	-40°C~+80°C
● Hardness	(HS) 70-75
● Characteristics	High elasticity. Wearing resistance.
● Applicable to Castors on	P.34



R-50TS	50	25	30	8	-	40 (390)
R-75TS	75	25	30	8	-	60 (580)
R-100TS	100	25	30	8	-	70 (680)

NB with steel/stainless steel bushing.

SEUW (for Stainless steel castors)

● Tire	UR (Antistatic polyurethane)
● Wheel center	SUS 304
● Bearing	NBS Stainless steel needle bearing
● Operating temp.	-30°C~+80°C
● Hardness	(HS) 85-88
● Volume resistance	10 ⁶ ~10 ⁸ Ω·cm*
● Characteristics	Antistatic. Oil resistance. Floor saving.
● Applicable to Castors on	P.37 P.41
*For reference only, not guaranteed.	



SEUW-100 NBS	100	35	42	10	10.0	150 (1470)
SEUW-125 NBS	125	42	56	12	11.5	210 (2050)
SEUW-150 NBS	150	45	56	12	12.0	250 (2450)

SPM (Semi-pneumatic tire)

● Tire	NR (85%), BR (15%)
● Wheel center	Die-cast aluminum
● Bearing	JBB Radial ball bearing
● Operating temp.	-30°C~+80°C
● Hardness	(HS) 60
● Characteristics	High elasticity. Shock resistance. Low noise.
● Applicable to Castors on	P.15 P.26 P.52 P.54



SPM-150 JBB	150	45	49	20	-	80 (780)
SPM-200 JBB	200	45	49	20	-	100 (980)

Blickle® SPO

● Tire	Reinforced nylon
● Wheel center	-
● Bearing	JBB Radial ball bearing
● Operating temp.	-25°C~+80°C
● Hardness	(R) 100-110
● Characteristics	Shock resistance. Low starting resistance.
● Applicable to Castors on	P.49

<Made in Germany>



SPO-75K JBB	75	32×2	82	10	-	300* (2940)
--------------------	----	------	----	----	---	----------------

NB with steel bushing.
*In case of single wheel.

SST ベアリングCB追加

● Tire	High rebound rubber
● Wheel center	Steel SPHC-P
● Bearing	JBB Radial ball bearing
● Operating temp.	-40°C~+90°C
● Hardness	(HS) 65-75
● Characteristics	High elasticity. Low starting resistance.
● Applicable to Castors on	P.7 P.13 P.25 P.27 P.31 P.51 P.53



SST-100 JBB CB	100	35	42	12	13.5	130 (1270)
SST-150 JBB CB**	150	45	55	20	15.0	200 (1960)
SST-200 JBB CB**	200	45	55	20	17.5	250 (2450)

ベアリングにCBを追加(100径のみJBBを削除)
**4km/hで使用の場合は、JBBの使用をお願いいたします。