


WSPK Type

Examples of model number formation

2	WSPK	6	-S	300	CM	H	/A
1	2	3	4	5	6	7	8

- 1** Q'ty of Nut **2** Part No. **3** Spline-shaft diameter
4 S:Solid, H:Hollow **5** Spline-shaft overall length
6 Preload : CT(Tight), CM(Middle), CL(Loose)
7 Accuracy symbol-Nomal(No symbol), High(H), Precision(P)
8 SUJ2(No symbol), Stainless steel(/A)

* When the grease nipple is necessary, please ask WON.



Part No.	Main dimensions													Length L	Max. length
	Outer Diameter D	Allowable Tolerance	L ₁	L ₂	D ₂	B	E	T	pcd	d _i	d	Allowable Tolerance			
WSPK 4 ⁽²⁾	8	0	12	7.9	21	10	4.6	2.5	15	3.4	4		100 150	200	
WSPK 5	10	-0.009	18	9.4	23	18	7	2.7	17	3.4	5	0 -0.012	100 150	200	
WSPK 6	12	0	21	12.4	25	20	7	2.7	19	3.4	6		150 200	300	
WSPK 8	15	-0.011	25	14.6	28	22	9	3.8	22	3.4	8	0 -0.015	150 200 250	500	
WSPK 10	19		30	18.2	36	28	10	4.1	28	4.5	10		200 300	600	
WSPK 12	21	0 -0.013	35	23	38	30	10	4	30	4.5	12	0	200 300 400	800	
WSPK 15	23		40	27	40	31	11	4.5	32	4.5	13.6	-0.018	200 300 400	1000	
WSPK 20	30		50	33	46	35	14	5.5	38	4.5	18.2		300 400 500 600	1000	
WSPK 25	37	0 -0.016	60	39.2	57	43	17	6.6	47	5.5	22.6	0 -0.021	300 400 500 600 800		
WSPK 30	45		70	43	65	50	21	7.5	54	6.6	27.2		400 500 600	1200	
WSPK 40	60	0 -0.019	100	70.8	93	73	26.6	12	73	9	37.2	0 -0.025	700 1100		

Note(1) As for the Static load rating moment T_M , the upside figures are for the value for one nut and the downside figure are for the values for 2 nuts to be closely adhered.

(2) There are no seals in WSP 4.