

# モールステーパホルダA型

BT<sup>®</sup>No.-MTA<sup>®</sup>(No.)-L

MORSE TAPER HOLDER (Type A)

» BBT対応 BBT Available



FIG.1





FIG.2



## ドリルシャंकと刃径 DRILL DIA. AND SHANK

SHANK		MT1	MT2	MT3	MT4	MT5
ドリル径 DRILL DIA.	以上MIN.	2.0	14.1	23.1	32.1	50.1
	以下MAX.	14.0	23.0	32.0	50.0	75.0

	MODEL	CODE	FIG.	MT No.	L	øD1	øC1	N/W (kg)
BT30 (BBT30)	-MTA1-045	10030	1	1	45	12.065	25	0.43
	-MTA2-060	10032	1	2	60	17.780	32	0.50
	-MTA3-080	10034	1	3	80	23.825	40	0.69
BT40 (BBT40)	-MTA1-045	11152	1	1	45	12.065	25	1.0
	-120	11154	2		120			1.3
	-MTA2-045	11156	1	2	45	17.780	32	1.0
	-120	11158	2		120			1.5
	-MTA3-075	11160	1	3	75	23.825	40	1.2
	-135	11162	2		135			1.8
	-MTA4-090	11164	1	4	90	31.267	50	1.4
	-165	11166	2		165			2.5
BT50 (BBT50)	-MTA1-045	13302	1	1	45	12.065	25	3.6
	-120	13304	2		120			3.9
	-180	13306	2		180			4.2
	-MTA2-045	13308	1	2	45	17.780	32	3.6
	-135	13310	2		135			4.2
	-180	13312	2		180			4.5
	-MTA3-045	13314	1	3	45	23.825	40	3.5
	-150	13316	2		150			4.5
	-180	13318	2		180			4.8
	-MTA4-075	13320	1	4	75	31.267	50	3.6
	-180	13322	2		180			5.2
	-MTA5-105	13324	1	5	105	44.399	65	3.9
	-210	13326	2		210			6.5

注: タング付MTシャंक刃具をご使用下さい。

NOTE: 1. For tongue type Morse taper shank cutting tools.

### ご注文例 ORDERING EXAMPLE

① **BT30** - ② **MTA** ③ **1** - ④ **045**

① シャंकサイズ Shank Size  
 ② 呼称 Holder's Name  
 ③ MT No. MT No.  
 ④ GL長さ L G.L. Length

BT series

HSK series

ST series

Versatile Tool

Cutting Tool

Accessories

Data