



These are casters that can simultaneously lock rotation of the mounting portion and rotation of wheels, and stopper lever types can be widely selected according to application.

ST SPECIAL TYPE



ST-100NU(H132), M16×40 ST-100NUSW-1, M16×40 ST-100NUSW-2, M16×40 ST-100NUSW-3, M16×40

Bracket = Trivalent unichrome coating

Product number	Stopper	Wheels	Wheel diameter	Wheel width	Mounting height	Screw	Pitch	Length	Opposite side	Eccentricity	Turning radius	Allowance load	Wheel weight
			D(mm)	W(mm)	H(mm)	T	L	N(mm)	M(mm)	E(mm)	R(mm)	daN(kgf)	(g)
ST-75	NRB(H104)	Not available	75	27	104	M12	1.75	35	21	26	65	70(71.4)	
	NRBSW	Available									92(*1)	70(71.4)	
	NU(H104)	Not available		25							65	70(71.4)	335
	NUSW	Available									92(*1)	70(71.4)	490
	UHF(H104)	Not available		26							65	70(71.4)	
	UHFSW	Available									92(*1)	70(71.4)	
ST-100	NRB(H132)	Not available	100	27	132	M16	2	40	23	29	80	70(71.4)	
	NRBSW	Available									93(*2)	70(71.4)	
	NU(H132)	Not available		25							80	70(71.4)	530
	NUSW	Available									93(*2)	70(71.4)	600
	UHF(H132)	Not available		28							80	70(71.4)	
	UHFSW	Available									93(*2)	70(71.4)	

*1 This is the turning radius of stopper type -1. As for -2, the turning radius increases for +12mm. As for -3, the turning radius increases for +4mm.
 *2 This is the turning radius of stopper type -1. As for -2, the turning radius increases for +2mm. As for -3, the turning radius increases for +4mm.
 * Be sure to wear shoes when operating the stopper.
 * If you operate the stopper by hand, you may get injured. Therefore, do not operate the stopper by hand.
 ● Allowable load is the allowable load when the stem is screwed in to the end.
 ★ Refer to P7 for the mounting method.

Wheel in use Refer to P155 for detailed specifications.



● Description of product number Please specify screw type and length.

ST - 100 NU SW - 3 , M16 × 40

Bracket type	Wheel diameter	Wheel type	Availability of a double stopper	Stopper type*	Screw	Length

*Stopper type
 -1: Resin stopper
 -2: Resin stopper equipped with the release lever
 -3: Steel plate stopper equipped with the release lever

- J
- PM
- J2
- RJ2
- SJ
- S
- E
- G
- L
- SA
- H
- CAL -H
- M
- PL
- Silence
- SUS -J2
- SUS -SJ
- SUS -S
- SUS -E
- SUS -H
- P
- SKY
- Equipped with adjuster foot
- Special
- Easy lock
- Wheels