



TOEI BRAND SCALE & PROTRACTOR

SCALE STOPPER your straight rule can get 1/10's graduation easily


- Vernier reading only with stopper for straight rule.
- It is possible to attach to JIS 1st class's straight rule.
- Scale Stopper can be used with straight rule as Vernier Caliper.




EXAMPLE




① In case of the same size's layout, this Scale Caliper can marked speedily.




④ The correct cutting is possible at 0.1mm step



② It is possible to use instead of Height Gauge and, it is not necessary to put on the surface plate.



⑤ It is convenient when the same size's welding.






③ It is possible to measure the length, depth & etc. correctly.

Model Number	Size (mm)	Min. Reading	Size of Stopper (mm)
SS300B	SS300	300	44L × 38W × 9t
SS600B	SS600	600	50L × 44W × 9t
SS1000B	SS1000	1000	50L × 50W × 9t
SS1500B	SS1500	1500	50L × 54W × 12t
SS2000B	SS2000	2000	50L × 54W × 12t
SS3000B	SS3000	3000	50L × 54W × 12t

SCALE CALIPER for speedy measurement of long size's materials

- It is possible to use this Scale Caliper instead of long size's Vernier Caliper with 1/10mm reading.
- About 1/10 price than Vernier Caliper.
- It is possible to measure the long length by one in light weight.

Model Number	Max. Range (mm)	Min. Reading	Scale	Head (mm)	Stopper (mm)
SC1000	1000	0.1 (mm)	JIS 1st class Hard Chrom	100 × 16 × 6t	50L × 50W × 9t
SC1500	1500				50L × 54W × 12t
SC2000	2000				50L × 54W × 12t
SC3000	3000		Head Chrom		



☆ THE COMPARISON OF SCALE CALIPER AND VERNIER CALIPER ☆

JIS 1ST CLASS'S SCALE	JIS 1ST CLASS'S VERNIER CALIPER
Length (mm)	MAX. Range (mm)
500 under	300
501 ~ 1000	600
1001 ~ 1500	1000
1501 ~ 2000	JIS Standard is nothing 1000 over