


# Shaft Supports - T-Shaped (Cast)

## Standard / Side Slit / Wide Side Slit


■ **Features:** Standard Type allows the shaft to be secured easily. Suitable when lengthwise space is limited.

■ **Standard**



RoHS10

Type	Material	Surface Treatment	Accessory
SHTBT	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHTBM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 1 pc. (SUS)
SHTBS	SUS304 Equivalent	-	Hex Socket Set Screw 1 pc. (SUS)
SHTBA	AC7A	Clear Anodize	




Cast Characters

Part Number Type	No.	D	H	L	H <sub>1</sub>	T	L <sub>1</sub>	d	L <sub>2</sub>	A	S	B <sub>1</sub>	B <sub>2</sub>	B <sub>3</sub>	Set Screw M	Mass g	Unit Price			
																	SHTBT	SHTBM	SHTBS	SHTBA
SHTBT SHTBM SHTBS SHTBA	815	8	15		24				18		6				M4	29 (10)				
	1020	10		42	30				21						M4	46 (16)				
	1220	12	20		32	10	32	5.5	20						M4	49 (17)				
	1320	13			32				25	24	8	14	8	2	M4	46 (16)				
	1625	16	25		48	40			30	30	10				M6	72 (25)				
	2025	20		60	43		45	6.6	30	30	10				M6	153 (53)				
	2030	20		60	48	16	45	6.6	30	30	10				M6	178 (62)				
	2530	25	30		70	50			35	35					M6	201 (70)				
	3030	30		84	53	20	64	9	44	42					M6	314 (109)				


⊕ Values in ( ) are the mass for aluminum products.

■ **Side Slit**



RoHS10

Type	Material	Surface Treatment	Accessory
SHTCT	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHTCM	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 1 pc. (SUS)
SHTCS	SUS304 Equivalent	-	Hex Socket Head Cap Screw 1 pc. (SUS)
SHTCA	AC7A	Clear Anodize	




Cast Characters

⊕ Slit is machined after the mounting hole D is bored to H7 tolerance. The tolerance may become H8 or so depending on the machining condition. ⊕ Pilot hole for tapped hole M may be through.

Part Number Type	No.	D	H	L	H <sub>1</sub>	T	L <sub>1</sub>	d	L <sub>2</sub>	A	S	E	C	B <sub>1</sub>	B <sub>2</sub>	B <sub>3</sub>	Tightening Screw M	Mass g	Unit Price			
																			SHTCT	SHTCM	SHTCS	SHTCA
SHTCT SHTCM SHTCS SHTCA	815	8	15	52	22		40		28	26		9					M4	61 (21)				
	1020	10		54	29		42		30	27		10					M4	81 (28)				
	1220	12	20		56	31	12	44	5.5	32	28	6					M4	90 (31)				
	1320	13		56	31		44	5.5	32	28	6						M4	87 (30)				
	1625	16	25		58	37		46		34	29						M6	107 (37)				
	2025	20		79	40		64	6.5	49	39.5	8						M6	220 (76)				
	2030	20		79	45	16	64	6.5	49	39.5	8						M6	254 (88)				
	2530	25	30		102	48		82	9	62	51	10	22	3			M8	248 (86)				
	3030	30		102	51	20	82	9	62	51	10	22	3				M8	477 (165)				


⊕ Values in ( ) are the mass for aluminum products.

■ **Wide Side Slit**



RoHS10

Type	Material	Surface Treatment	Accessory
SHTCTN	S45C	Black Oxide	Hex Socket Head Cap Screw 1 pc.
SHTCMN	Equivalent	Electroless Nickel Plating	Hex Socket Head Cap Screw 1 pc. (SUS)



Cast Characters

⊕ Slit is machined after the mounting hole D is bored to H7 tolerance. The tolerance may become H8 or so depending on the machining condition. ⊕ Pilot hole for tapped hole M may be through.

Part Number Type	D	H	L	H <sub>1</sub>	T	T <sub>1</sub>	L <sub>1</sub>	d	L <sub>2</sub>	S	E	C	Tightening Screw M	d <sub>1</sub>	d <sub>2</sub>	ℓ	Weight g	Unit Price	
																		SHTCTN	SHTCMN
SHTCTN SHTCMN	10			30	20	-	50		38	6	12		M6	11	6.6	6.5	181		
	12	20	62	38	25				12.5				M6				176		
	16	25		48	25				8	20.5			M6				264		
	20		85	48	30	15	70		8	20.5			M8	14	9		614		
	25	30		53	40				7	10	24	3	M8				574		
	30		110	53	40	20	90		7	10	24	3	M8				1038		

Ordering Example  
 Part Number  
 SHTBT3030  
 SHTCS2025  
 SHTCTN20