



※ 1 表 1

No.	Part name	零件名称	Material 材料
①	Resin guide retainer	树脂导向本体	Polyacetal POM (工程塑料)
②	Fixed pipe	固定套管	SS400
③	Bolts used	安装螺栓	SCM435

Example order

Order names	Quantity
RG23-050	100

订货例

型式	数量
RG23-050	100

② Table of standards 规格表

Model 型号	D	L	L1	The size of applicable bolt 使用螺栓	F	Applicable standard 适用弹簧规格
RG 23 - 050	23	50.0	38.0	M 12 X 65 X P = 1.75	27.0	TL50 · TM50 TH50 · TB50
RG 23 - 075		75.0	63.0	M 12 X 90 X P = 1.75		
RG 23 - 100		100.0	88.0	M 12 X 115 X P = 1.75		
RG 23 - 125		125.0	113.0	M 12 X 140 X P = 1.75		
RG 26 - 050	26	50.0	38.0	M 12 X 65 X P = 1.75	27.0	TF 50
RG 26 - 075		75.0	63.0	M 12 X 90 X P = 1.75		
RG 26 - 100		100.0	88.0	M 12 X 115 X P = 1.75		
RG 26 - 125		125.0	113.0	M 12 X 140 X P = 1.75		
RG 28 - 050	28	50.0	38.0	M 12 X 65 X P = 1.75	27.0	TL60 · TM60 TH60 · TB60
RG 28 - 075		75.0	63.0	M 12 X 90 X P = 1.75		
RG 28 - 100		100.0	88.0	M 12 X 115 X P = 1.75		
RG 28 - 125		125.0	113.0	M 12 X 140 X P = 1.75		
RG 31 - 050	31	50.0	38.0	M 12 X 65 X P = 1.75	27.0	TF 60
RG 31 - 075		75.0	63.0	M 12 X 90 X P = 1.75		
RG 31 - 100		100.0	88.0	M 12 X 115 X P = 1.75		
RG 31 - 125		125.0	113.0	M 12 X 140 X P = 1.75		
RG 36 - 050	36	50.0	38.0	M 12 X 65 X P = 1.75	27.0	TF70 · TL70 · TM70 TH70 · TB70
RG 36 - 075		75.0	63.0	M 12 X 90 X P = 1.75		
RG 36 - 100		100.0	88.0	M 12 X 115 X P = 1.75		
RG 36 - 125		125.0	113.0	M 12 X 140 X P = 1.75		