


## SW·SW-N·SW-T SERIES



## Color Type

Series	Color code	Color
SW	S	Light gray
	B	Black
SW-N	G	Gray
SW-T	B	Black

## SW standard

ABS UL94HB

## Part no. / Dimensions

• Please suffix color code at the end of part number □ when ordering SW series.

Part no.	W	H	D	Weight(g)
SW- 15□	10	10	15	1
SW- 20□	15	15	20	2
SW- 30□	20	18	30	4
SW- 40□	30	20	40	10
SW- 50□	35	25	50	14
SW- 53□	36	11	53	10
SW- 55□	40	20	55	17
SW- 60□	18	17	60	9
SW- 65□	45	25	65	21
SW- 75□	50	30	75	32
SW- 85□	60	40	85	43
SW- 90□	25	21	90	17
SW- 95□	58	18	95	34
SW-100□	65	35	100	55
SW-120□	60	24	120	50
SW-125□	70	40	125	77
SW-130□	40	25	130	43

## SW-N flame-resistant

ABS UL94V-1 / UL94V-0

## Part no. / Dimensions

Part no.	W	H	D	UL- class	Weight(g)
SW-N 20G	15	15	20	UL94V-1	3
SW-N 30G	20	18	30	UL94V-1	5
SW-N 40G	30	20	40	UL94V-0	11
SW-N 50G	35	25	50	UL94V-0	17
SW-N 55G	40	20	55	UL94V-0	19
SW-N 65G	45	25	65	UL94V-0	23
SW-N 75G	50	30	75	UL94V-0	35
SW-N 85G	60	40	85	UL94V-0	50
SW-N 95G	58	18	95	UL94V-0	37
SW-N100G	65	35	100	UL94V-0	60
SW-N120G	60	24	120	UL94V-0	56
SW-N125G	70	40	125	UL94V-0	85
SW-N130G	40	25	130	UL94V-0	48

## SW-T heat-resistant

ABS Heat distortion temperature 100°C

## Part no. / Dimensions

Part no.	W	H	D	Weight(g)
SW-T 20B	15	15	20	2
SW-T 40B	30	20	40	9
SW-T 55B	40	20	55	16
SW-T 75B	50	30	75	30
SW-T 95B	58	18	95	31
SW-T100B	65	35	100	50