


Guides

V-Shaped / Plate


■ **Features:** Can be used as a round workpiece guide or receiver.

■ **V-Shaped Type**



RoHS10

Type	Material	Hardness	Surface Treatment
WGVA	S45C	-	-
WGVB		-	Black Oxide
WGVM		-	Electroless Nickel Plating
WGVH		40HRC~	Black Oxide
WGVR	-	-	Electroless Nickel Plating
WGVJ	Polyacetal	-	-
WGVN	MC Nylon	-	-




1.6/


⚠ Possible to receive Ø5 ~ Ø30 round poles.

Part Number		Unit Price						
Type	L Selection	WGVA	WGVB	WGVM	WGVH	WGVR	WGVJ	WGVN
WGVA WGVB WGVM WGVH WGVR WGVJ WGVN	25							
	35							

Ordering Example
Part Number
WGVA25
WGVJ35




■ **Plate Type**



RoHS10

Type	Material	Surface Treatment
WGTB	S45C	Black Oxide
WGTM	Equivalent	Electroless Nickel Plating
WGTJ	Polyacetal	-





6.3/

Part Number		B	L	T Selection	G	d	Unit Price		
Type	A	1mm Increment	10mm Increment				WGTB	WGTM	WGTJ
WGTB WGTM WGTJ	16	8~12	50~200	5	6	4.5			
	19								
	22	11~15	60~200	9	8	5.5			
	25								
	32								
		14~25	80~200	12	10	6.5			

Ordering Example
Part Number - B - L - T
WGTB16 - B8 - L50 - T5

Alterations
Part Number - B - L - T - (CC, SHC)
WGTB16 - B8 - L100 - T5 - CC

Alterations	Both Sides Cut Type	Partial Hardening
Spec.	 Cuts symmetrically. ⚠ L ≥ minLx2	 ⚠ Applicable to WGTB and WGTM. (45 ~ 50HRC) Depth 0.5 ~ 1.5mm
Code	CC	SHC