


Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Hand Tap (for whitworth thread)

Com Drawing Surface Treatment Non-coat




T-HT Series

- Features**
- Used to make threaded hole and to clean it out.
 - For repairing and manufacturing ridge.
- Use**
- Work Material: Iron, Light Metal.
- Specs**
- Machining Thread: Whitworth Thread
- Materials**
- Low-Alloy Steel (SKS)
- Origin**
- Japan

Warning

- Cannot be used for stainless steel materials.



Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

| Order Code | Item No. | Price (per piece) | MSRP (per piece) | Tip | Precision | Nominal Dimension | Number of Ridges | Screw Length (mm) | Total Length (mm) | Shank Diameter (mm) | Shank Square Part (mm) | Pilot Hole Diameter (mm) | SPQ (piece) |
|------------|---------------|-------------------|------------------|-----------|-------------|-------------------|------------------|-------------------|-------------------|---------------------|------------------------|--------------------------|-------------|
| 441-5558 | T-HT1/8W40-1 | ¥ 421 | ¥ 520 | Tip | JIS Class 3 | W1/8 | 40 | 18 | 46 | 4.0 | 3.2 | 2.6 | 10 |
| 441-5566 | T-HT1/8W40-2 | ¥ 421 | ¥ 520 | Medium | JIS Class 3 | W1/8 | 40 | 18 | 46 | 4.0 | 3.2 | 2.6 | 10 |
| 441-5574 | T-HT1/8W40-3 | ¥ 421 | ¥ 520 | Bottoming | JIS Class 3 | W1/8 | 40 | 18 | 46 | 4.0 | 3.2 | 2.6 | 10 |
| 441-5582 | T-HT3/16W24-1 | ¥ 454 | ¥ 560 | Tip | JIS Class 3 | W3/16 | 24 | 22 | 60 | 5.5 | 4.5 | 3.8 | 10 |
| 441-5591 | T-HT3/16W24-2 | ¥ 454 | ¥ 560 | Medium | JIS Class 3 | W3/16 | 24 | 22 | 60 | 5.5 | 4.5 | 3.8 | 10 |
| 441-5604 | T-HT3/16W24-3 | ¥ 454 | ¥ 560 | Bottoming | JIS Class 3 | W3/16 | 24 | 22 | 60 | 5.5 | 4.5 | 3.8 | 10 |
| 441-5612 | T-HT1/4W20-1 | ¥ 551 | ¥ 680 | Tip | JIS Class 3 | W1/4 | 20 | 24 | 62 | 6.0 | 4.5 | 5.1 | 10 |
| 441-5621 | T-HT1/4W20-2 | ¥ 551 | ¥ 680 | Medium | JIS Class 3 | W1/4 | 20 | 24 | 62 | 6.0 | 4.5 | 5.1 | 10 |
| 441-5639 | T-HT1/4W20-3 | ¥ 551 | ¥ 680 | Bottoming | JIS Class 3 | W1/4 | 20 | 24 | 62 | 6.0 | 4.5 | 5.1 | 10 |
| 441-5647 | T-HT5/16W18-1 | ¥ 689 | ¥ 850 | Tip | JIS Class 3 | W5/16 | 18 | 30 | 70 | 6.1 | 5.0 | 6.6 | 10 |
| 441-5655 | T-HT5/16W18-2 | ¥ 689 | ¥ 850 | Medium | JIS Class 3 | W5/16 | 18 | 30 | 70 | 6.1 | 5.0 | 6.6 | 10 |
| 441-5663 | T-HT5/16W18-3 | ¥ 689 | ¥ 850 | Bottoming | JIS Class 3 | W5/16 | 18 | 30 | 70 | 6.1 | 5.0 | 6.6 | 10 |
| 441-5671 | T-HT3/8W16-1 | ¥ 940 | ¥ 1,160 | Tip | JIS Class 3 | W3/8 | 16 | 35 | 75 | 7.0 | 5.5 | 8.0 | 10 |
| 441-5680 | T-HT3/8W16-2 | ¥ 940 | ¥ 1,160 | Medium | JIS Class 3 | W3/8 | 16 | 35 | 75 | 7.0 | 5.5 | 8.0 | 10 |
| 441-5698 | T-HT3/8W16-3 | ¥ 940 | ¥ 1,160 | Bottoming | JIS Class 3 | W3/8 | 16 | 35 | 75 | 7.0 | 5.5 | 8.0 | 10 |
| 441-5701 | T-HT1/2W12-1 | ¥ 1,328 | ¥ 1,640 | Tip | JIS Class 3 | W1/2 | 12 | 42 | 85 | 9.0 | 7.0 | 10.7 | 10 |
| 441-5710 | T-HT1/2W12-2 | ¥ 1,328 | ¥ 1,640 | Medium | JIS Class 3 | W1/2 | 12 | 42 | 85 | 9.0 | 7.0 | 10.7 | 10 |
| 441-5728 | T-HT1/2W12-3 | ¥ 1,328 | ¥ 1,640 | Bottoming | JIS Class 3 | W1/2 | 12 | 42 | 85 | 9.0 | 7.0 | 10.7 | 10 |
| 854-9636 | T-HT5/8W11-1 | ¥ 2,576 | ¥ 3,180 | Tip | JIS Class 3 | W5/8 | 11 | 45 | 95 | 12.0 | 9.0 | 13.5 | 1 |
| 854-9637 | T-HT5/8W11-2 | ¥ 2,576 | ¥ 3,180 | Medium | JIS Class 3 | W5/8 | 11 | 45 | 95 | 12.0 | 9.0 | 13.5 | 1 |
| 854-9638 | T-HT5/8W11-3 | ¥ 2,576 | ¥ 3,180 | Bottoming | JIS Class 3 | W5/8 | 11 | 45 | 95 | 12.0 | 9.0 | 13.5 | 1 |
| 854-9625 | T-HT3/4W10-1 | ¥ 4,253 | ¥ 5,250 | Tip | JIS Class 3 | W3/4 | 10 | 50 | 105 | 14.0 | 11.0 | 16.5 | 1 |
| 854-9626 | T-HT3/4W10-2 | ¥ 4,253 | ¥ 5,250 | Medium | JIS Class 3 | W3/4 | 10 | 50 | 105 | 14.0 | 11.0 | 16.5 | 1 |
| 854-9627 | T-HT3/4W10-3 | ¥ 4,253 | ¥ 5,250 | Bottoming | JIS Class 3 | W3/4 | 10 | 50 | 105 | 14.0 | 11.0 | 16.5 | 1 |
| 854-9644 | T-HT7/8W9-1 | ¥ 5,670 | ¥ 7,000 | Tip | JIS Class 3 | W7/8 | 9 | 55 | 115 | 17.0 | 13.0 | 19.5 | 1 |
| 854-9645 | T-HT7/8W9-2 | ¥ 5,670 | ¥ 7,000 | Medium | JIS Class 3 | W7/8 | 9 | 55 | 115 | 17.0 | 13.0 | 19.5 | 1 |
| 854-9646 | T-HT7/8W9-3 | ¥ 5,670 | ¥ 7,000 | Bottoming | JIS Class 3 | W7/8 | 9 | 55 | 115 | 17.0 | 13.0 | 19.5 | 1 |
| 854-9601 | T-HT1W8-1 | ¥ 8,035 | ¥ 9,920 | Tip | JIS Class 3 | W1 | 8 | 60 | 125 | 20.0 | 15.0 | 22.0 | 1 |
| 854-9602 | T-HT1W8-2 | ¥ 8,035 | ¥ 9,920 | Medium | JIS Class 3 | W1 | 8 | 60 | 125 | 20.0 | 15.0 | 22.0 | 1 |
| 854-9603 | T-HT1W8-3 | ¥ 8,035 | ¥ 9,920 | Bottoming | JIS Class 3 | W1 | 8 | 60 | 125 | 20.0 | 15.0 | 22.0 | 1 |

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Hand Tap Set (for whitworth thread)

Com Drawing Surface Treatment Non-coat




T-HT-S Series

- Features**
- Used to make threaded hole and to clean it out.
 - For repairing and manufacturing ridge.
 - Tungsten hand set tap.
- Use**
- Work Material: Iron, Light Metal.
- Specs**
- Machining Thread: Whitworth Thread
- Materials**
- Low-Alloy Steel (SKS)
- Origin**
- Japan

Warning

- Cannot be used for stainless steel materials.



Order Unit: 1 Set

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

| Order Code | Item No. | Price (per set) | MSRP (per set) | Set Content | Precision | Nominal Dimension | Number of Ridges | Screw Length (mm) | Total Length (mm) | Shank Diameter (mm) | Shank Square Part (mm) | SPQ (set) |
|------------|---------------|-----------------|----------------|----------------------|-------------|-------------------|------------------|-------------------|-------------------|---------------------|------------------------|-----------|
| 480-6310 | T-HT1/8W40-S | ¥ 1,256 | ¥ 1,550 | Tip/Medium/Bottoming | JIS Class 3 | W1/8 | 40 | 18 | 46 | 4.0 | 3.2 | 10 |
| 480-6328 | T-HT3/16W24-S | ¥ 1,337 | ¥ 1,650 | Tip/Medium/Bottoming | JIS Class 3 | W3/16 | 24 | 22 | 60 | 5.5 | 4.5 | 10 |
| 480-6301 | T-HT1/4W20-S | ¥ 1,636 | ¥ 2,020 | Tip/Medium/Bottoming | JIS Class 3 | W1/4 | 20 | 24 | 62 | 6.0 | 4.5 | 10 |
| 480-6425 | T-HT5/16W18-S | ¥ 2,050 | ¥ 2,530 | Tip/Medium/Bottoming | JIS Class 3 | W5/16 | 18 | 30 | 70 | 6.1 | 5.0 | 10 |
| 480-6379 | T-HT3/8W16-S | ¥ 2,811 | ¥ 3,470 | Tip/Medium/Bottoming | JIS Class 3 | W3/8 | 16 | 35 | 75 | 7.0 | 5.5 | 10 |
| 480-6255 | T-HT1/2W12-S | ¥ 3,978 | ¥ 4,910 | Tip/Medium/Bottoming | JIS Class 3 | W1/2 | 12 | 42 | 85 | 9.0 | 7.0 | 10 |
| 854-9639 | T-HT5/8W11-S | ¥ 7,727 | ¥ 9,540 | Tip/Medium/Bottoming | JIS Class 3 | W5/8 | 11 | 45 | 95 | 12.0 | 9.0 | 1 |
| 854-9628 | T-HT3/4W10-S | ¥ 12,766 | ¥ 15,760 | Tip/Medium/Bottoming | JIS Class 3 | W3/4 | 10 | 50 | 105 | 14.0 | 11.0 | 1 |
| 854-9647 | T-HT7/8W9-S | ¥ 17,019 | ¥ 21,010 | Tip/Medium/Bottoming | JIS Class 3 | W7/8 | 9 | 55 | 115 | 17.0 | 13.0 | 1 |
| 854-9604 | T-HT1W8-S | ¥ 24,106 | ¥ 29,760 | Tip/Medium/Bottoming | JIS Class 3 | W1 | 8 | 60 | 125 | 20.0 | 15.0 | 1 |

Contact us:0120-509-849 <http://www.orange-book.com/>

Threading Tools

Spiral Fluted Taps

Point Taps

Roll Taps

Hand Taps

Hexagonal Shank Tapping Drills

Tap Holders

Taps for Pipe

Thread Mills for Machining Center

Dies

Thread Repair Tools

Tap and Bolt Burr Removing Tools

Sprew

For other cutting tools, see p. 1-805 to 1006