


Lift Pins


■ **Features:** Useable for lifting work objects that require isolation from metal contacts. A 50% more economical length selectable type is introduced.

■ **Lift Pins**



RoHS 10

L Selectable	Type		Main Body	Material	
	L Configurable	L, B Configurable		Main Body	Tip
-	LPCE	LPFCE	SUS304	Ceramic (Alumina 99)	
LPEPK	LPPK	LPFPK		PEEK	
-	LPMC	LPFMC		MC Nylon	



■ **L Selectable Type**

Part Number		L Selection	B Fixed	M (Coarse)	H	W	SR	Unit Price		
Type	D							L 25, 50	L 75, 100	L 120
LPEPK	3	25 50 75 100 120	4.5	3	6	5	1.2			
	4		6	4	8	7				
	5		7.5	5	9	7	2			
	6		9	6	10	8				

■ **L Configurable Type**

Part Number		L 1mm Increment	B Fixed	M (Coarse)	H	W	SR	Unit Price					
Type	D							L15-50			L51-120		
								LPCE	LPPK	LPMC	LPCE	LPPK	LPMC
LPCE LPPK LPMC	3	15~120	4.5	3	6	5	1.2						
	4		6	4	8	7							
	5		7.5	5	9	7	2						
	6	9	6	10	8								
	8	20~120	12	8	12	10	3.2						
	10		15	10	15	13							

■ **L, B Configurable Type**

Part Number		L 1mm Increment	B 0.5mm Increment	M (Coarse)	H	W	SR	Unit Price					
Type	D							L15-50			L51-120		
								LPFCE	LPFPK	LPFMC	LPFCE	LPFPK	LPFMC
LPFCE LPFPK LPFMC	3	15~120	5.0~9.0	3	6	5	1.2						
	4		6.5~12.0	4	8	7							
	5		8.0~15.0	5	9	7	2						
	6	9.5~18.0	6	10	8								
	8	20~120	12.5~24.0	8	12	10	3.2						
	10		15.5~30.0	10	15	13							

① L+B≤135



Ordering Example

Part Number	-	L	-	B	
LPEPK3	-	120			(L Selectable)
LPCE4	-	72			(L Configurable)
LPFCE5	-	75	-	B9.0	(L, B Configurable)



Example

Suitable for lifting high temperature objects and objects that are not to come in contact with metals.

