

Disk Papers

For Disc Grinders, see p. 5-209 to 226/For Adapter, see p. 5-921 The number next to the logo mark indicates items in stock for each brand.

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

TRUSCO Stock 38,650 Items

Disc Paper "GP Top"



Com Drawing SDS
Chemical Content Inspection



GPCO-10016

- Features**
- Silicon carbide abrasive material with high hardness is used.
 - Clogging was prevented with the use of coarse abrasive grains (#24).
 - Finishing the surface without deep cutting.
- Use**
- Optimum for chipping of concrete, stone, glass, roof tile and part repair.
 - Pre-processing of water pipe lining.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Materials**
- Silicone Carbide Abrasive
- Accessories**
- Including 10 pieces per 15mm hole adapter box (separately sold item no. 5 pieces included: GPTAS-5P)
- Origin**
- Japan



Estimated Unit Price per Sheet
¥729

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
299-4356	GPCO-10016	¥7,290	¥9,000	24	100 x 25 x 16	13600	45	10	10	800

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

"GP Top" for Stainless Steel



Com Drawing



TGPS100-60

- Features**
- Does not cause clogging or burns even when polishing stainless steel.
 - Stable grinding performance lasts from initial polishing to the end of use.
- Use**
- Welding bead removal, burr removal, and chamfering of stainless steel.
 - Polishing of difficult-to-grind materials such as stainless steel.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Materials**
- Zirconia abrasive material
- Accessories**
- Including 5 pieces per 15mm hole adapter box (separately sold item no. 5 pieces included: GPTAS-5P)
- Origin**
- Japan

Estimated Unit Price per Sheet
¥567

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
768-3383	TGPS100-40	¥2,835	¥3,500	40	100 x 22 x 16	13600	50	5	20	515
768-3391	TGPS100-60	¥2,835	¥3,500	60	100 x 22 x 16	13600	60	5	20	470
768-3405	TGPS100-80	¥2,835	¥3,500	80	100 x 22 x 16	13600	60	5	20	440

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Disc Paper "GP Top" Premium Double Flap




Com Drawing SDS
Chemical Content Inspection



GPPW-10016Z: 60

- Features**
- Disc paper that can grind away chunks like a whetstone.
 - Its double flap makes it less likely for burns to be created.
- Use**
- Grinding and polishing of difficult-to-cut material such as stainless steel.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Materials**
- Zirconia abrasive material
- Accessories**
- Including 10 pieces per 15mm hole adapter box (separately sold item no. 5 pieces included: GPTAS-5P)
- Origin**
- Japan



Estimated Unit Price per Sheet
¥527

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (kg/box)
299-4364	GPPW-10016Z	36	¥5,265	¥6,500	36	100 x 20 x 16	13600	56	10	10	1.23
299-4372	GPPW-10016Z	40	¥5,265	¥6,500	40	100 x 20 x 16	13600	60	10	10	1.18
299-4381	GPPW-10016Z	60	¥5,265	¥6,500	60	100 x 20 x 16	13600	68	10	10	1.10
299-4399	GPPW-10016Z	80	¥5,265	¥6,500	80	100 x 20 x 16	13600	72	10	10	1.05

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

Welding Bead Removal Disc



Com Drawing



TCD10015-C-60

- Features**
- A ceramic disc designed with a focus on grinding performance.
 - Has greater grinding performance than offset whetstones and flexible whetstones which increases work efficiency.
 - Sharp surface finishing is possible.
- Use**
- Welding bead removal, burring, chamfer, rust removal, paint removal, polishing of stainless steel/standard steel.
- Specs**
- Max Working Peripheral Velocity: 72m/s (4300m/min)
- Materials**
- Ceramic Abrasive
- Accessories**
- Including 5 pieces per 15mm hole adapter box (separately sold item no. 5 pieces included: GPTAS-5P)
- Origin**
- Japan



Estimated Unit Price per Sheet
¥454

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
436-8991	TCD10015-C-40	¥2,268	¥2,800	40	100 x 22 x 16	13600	36	5	10	65
436-9009	TCD10015-C-60	¥2,268	¥2,800	60	100 x 25 x 16	13600	36	5	10	61
436-9017	TCD10015-C-80	¥2,268	¥2,800	80	100 x 25 x 16	13600	36	5	10	59

Contact us:0120-509-849 <http://www.orange-book.com/>