

Flap Wheels with Shaft (shaft diameter 6mm, hexagon shaft)

The number next to the logo mark indicates items in stock for each brand.

TRUSCO



Stock 38,650 Items

Spin Screw Type Flap Wheel (shaft replacement type)




Com Drawing SDS



SF Type

- Features**
- The shaft is screw thread in, you can detach with one touch.
 - You can replace the shaft while attaching it to the chuck.
 - By using the spin shaft sold separately, work can be done by replacing the shaft whose shaft length is standard length (40mm) and deep hole (100mm).
- Use**
- Rust remover, burring, blazing.
 - Polishing of cylindrical interior, corner etc.
 - Working Tool: Straight-type grinder, electric drill, drill press, rechargeable impact screwdriver (when hexagonal shaft is used)
- Origin**
- Japan



Item No.	Max Working Rotation Speed (rpm)
SF-3025	20000
SF-4025 to 6025	18000

Estimated Unit Price per Piece
¥473 to ¥629

Warning
•Spinning axle is sold separately.


Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Box

SPQ: 20 Boxes

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	Weight (g/box)	Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	Weight (g/box)
275-8253	SF-3025	40	¥2,365	¥2,920	40	30 x 25	Approx. 36	5	132	275-8458	SF-5025	40	¥2,592	¥3,200	40	50 x 25	Approx. 52	5	283
275-8261	SF-3025	60	¥2,365	¥2,920	60	30 x 25	Approx. 55	5	133	275-8466	SF-5025	60	¥2,592	¥3,200	60	50 x 25	Approx. 82	5	290
275-8270	SF-3025	80	¥2,365	¥2,920	80	30 x 25	Approx. 64	5	131	275-8474	SF-5025	80	¥2,592	¥3,200	80	50 x 25	Approx. 94	5	282
275-8288	SF-3025	100	¥2,365	¥2,920	100	30 x 25	Approx. 70	5	130	275-8482	SF-5025	100	¥2,592	¥3,200	100	50 x 25	Approx. 107	5	272
275-8296	SF-3025	120	¥2,365	¥2,920	120	30 x 25	Approx. 68	5	137	275-8491	SF-5025	120	¥2,592	¥3,200	120	50 x 25	Approx. 102	5	300
275-8300	SF-3025	150	¥2,365	¥2,920	150	30 x 25	Approx. 75	5	138	275-8504	SF-5025	150	¥2,592	¥3,200	150	50 x 25	Approx. 107	5	301
275-8318	SF-3025	180	¥2,365	¥2,920	180	30 x 25	Approx. 77	5	138	275-8512	SF-5025	180	¥2,592	¥3,200	180	50 x 25	Approx. 114	5	302
275-8326	SF-3025	240	¥2,365	¥2,920	240	30 x 25	Approx. 90	5	130	275-8521	SF-5025	240	¥2,592	¥3,200	240	50 x 25	Approx. 137	5	286
275-8334	SF-3025	320	¥2,365	¥2,920	320	30 x 25	Approx. 95	5	126	275-8539	SF-5025	320	¥2,592	¥3,200	320	50 x 25	Approx. 146	5	280
275-8342	SF-3025	400	¥2,365	¥2,920	400	30 x 25	Approx. 100	5	126	275-8547	SF-5025	400	¥2,592	¥3,200	400	50 x 25	Approx. 148	5	276
275-8351	SF-4025	40	¥2,365	¥2,920	40	40 x 25	Approx. 36	5	174	275-8555	SF-6025	40	¥3,143	¥3,880	40	60 x 25	Approx. 60	5	365
275-8369	SF-4025	60	¥2,365	¥2,920	60	40 x 25	Approx. 58	5	182	275-8563	SF-6025	60	¥3,143	¥3,880	60	60 x 25	Approx. 90	5	370
275-8377	SF-4025	80	¥2,365	¥2,920	80	40 x 25	Approx. 64	5	182	275-8571	SF-6025	80	¥3,143	¥3,880	80	60 x 25	Approx. 105	5	370
275-8385	SF-4025	100	¥2,365	¥2,920	100	40 x 25	Approx. 71	5	176	275-8580	SF-6025	100	¥3,143	¥3,880	100	60 x 25	Approx. 115	5	373
275-8393	SF-4025	120	¥2,365	¥2,920	120	40 x 25	Approx. 71	5	188	275-8598	SF-6025	120	¥3,143	¥3,880	120	60 x 25	Approx. 120	5	380
275-8407	SF-4025	150	¥2,365	¥2,920	150	40 x 25	Approx. 75	5	185	275-8601	SF-6025	150	¥3,143	¥3,880	150	60 x 25	Approx. 124	5	393
275-8415	SF-4025	180	¥2,365	¥2,920	180	40 x 25	Approx. 80	5	180	275-8610	SF-6025	180	¥3,143	¥3,880	180	60 x 25	Approx. 125	5	332
275-8423	SF-4025	240	¥2,365	¥2,920	240	40 x 25	Approx. 90	5	170	275-8628	SF-6025	240	¥3,143	¥3,880	240	60 x 25	Approx. 155	5	365
275-8431	SF-4025	320	¥2,365	¥2,920	320	40 x 25	Approx. 100	5	168	275-8636	SF-6025	320	¥3,143	¥3,880	320	60 x 25	Approx. 163	5	353
275-8440	SF-4025	400	¥2,365	¥2,920	400	40 x 25	Approx. 105	5	168	275-8644	SF-6025	400	¥3,143	¥3,880	400	60 x 25	Approx. 165	5	352



SS-6040

(spinning axle (shaft diameter 6mm))



SSB-6040

(spinning axle (hexagonal shaft))



SS-6100

(spinning axle (shaft diameter 6mm))

- Features**
- The shaft is screw thread in, you can detach with one touch.
 - Can replace the polishing section with the shaft attached to the chuck of the power section.
- Specs**
- Mounting Tool: Straight-Type Grinder Flexible Shaft, Rechargeable Impact Drivers (hexagonal shaft)

Warning
•Please be sure to check the conditions of use.

Spinning Axle (6mm)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shaft Diameter (mm)	Shaft Length (mm)	SPQ (piece)	Weight (g)
275-8652	SS-6040	¥194	¥240	6	40	1	11.2
275-8661	SS-6100	¥384	¥475	6	100	1	28.0

Spinning Shaft (hexagon shaft)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Shaft Diameter (mm)	Shaft Length (mm)	SPQ (piece)	Weight (g)
437-4533	SSB-6040	¥194	¥240	6.35	40	1	17

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO



Stock 38,650 Items

Super Grinding Flap Wheel (diagonally embedded type, shaft diameter 6mm)



Com Drawing SDS



HF4025Z-60

Estimated Unit Price per Piece
¥719 to ¥1,078

- Features**
- A flap wheel having double the grinding speed and more than double the speed and durability with grinding volume compared to a normal wheel.
 - The flaps are embedded in a diagonal manner.
 - Uses a zirconia abrasive material which is suitable for heavy grinding and has a long life.
- Use**
- Rust remover, burring, polishing of pipe's inner side.
 - Polishing of metal, woodwork curved surfaces and different type of goods.
- Specs**
- Max Working Rotation Speed: 20000rpm
 - Working Tool: Straight-type grinder.
 - Origin: Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Blade Number (sheet)	Q'ty Per Box (piece)	SPQ (box)	Weight (g/box)
768-2859	HF2525Z-40	¥3,596	¥4,440	40	25 x 25 x 6 x 40	Approx. 19	5	10	155
768-2867	HF2525Z-60	¥3,596	¥4,440	60	25 x 25 x 6 x 40	Approx. 25	5	10	155
768-2875	HF2525Z-80	¥3,596	¥4,440	80	25 x 25 x 6 x 40	Approx. 29	5	10	155
768-2883	HF3025Z-40	¥3,596	¥4,440	40	30 x 25 x 6 x 40	Approx. 33	5	10	192
768-2891	HF3025Z-60	¥3,596	¥4,440	60	30 x 25 x 6 x 40	Approx. 37	5	10	192
768-2905	HF3025Z-80	¥3,596	¥4,440	80	30 x 25 x 6 x 40	Approx. 39	5	10	192
484-6923	HF4025Z-40	¥3,596	¥4,440	40	40 x 25 x 6 x 40	Approx. 29	5	10	268
484-6931	HF4025Z-60	¥3,596	¥4,440	60	40 x 25 x 6 x 40	Approx. 38	5	10	271
484-6940	HF4025Z-80	¥3,596	¥4,440	80	40 x 25 x 6 x 40	Approx. 44	5	10	270
484-6958	HF5025Z-40	¥3,670	¥4,530	40	50 x 25 x 6 x 40	Approx. 42	5	10	365
484-6966	HF5025Z-60	¥3,670	¥4,530	60	50 x 25 x 6 x 40	Approx. 53	5	10	371
484-6974	HF5025Z-80	¥3,670	¥4,530	80	50 x 25 x 6 x 40	Approx. 59	5	10	361
484-6982	HF6025Z-40	¥4,293	¥5,300	40	60 x 25 x 6 x 40	Approx. 51	5	10	501
484-6991	HF6025Z-60	¥4,293	¥5,300	60	60 x 25 x 6 x 40	Approx. 61	5	10	503
484-7008	HF6025Z-80	¥4,293	¥5,300	80	60 x 25 x 6 x 40	Approx. 71	5	10	492
484-7016	HF8025Z-40	¥5,387	¥6,650	40	80 x 25 x 6 x 40	Approx. 64	5	10	787
484-7024	HF8025Z-60	¥5,387	¥6,650	60	80 x 25 x 6 x 40	Approx. 80	5	10	770
484-7032	HF8025Z-80	¥5,387	¥6,650	80	80 x 25 x 6 x 40	Approx. 93	5	10	754

Contact us: 0120-509-849 <http://www.orange-book.com/>

