


The number next to the logo mark indicates items in stock for each brand.

TRUSCO Stock **38,650** Items

Super Thin Flex Diamond File



- Features**
- A flat file with a double-sided diamond coating on a flexible substrate.
 - With an extremely thin blades having a thickness of less than 1mm, it is possible to process narrow grooves and narrow gaps that cannot be processed with conventional diamond files.
 - Because the base of the file uses spring steel, it is flexible, has strength, and is light.
- Use**
- For polishing of narrow grooves and narrow gaps that can not be processed with conventional files.
 - For curved surface polishing.
 - For processing of slit portions.
- Origin**
- Israel

Example



Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Shape	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
764-4981	TSF05-120	¥11,109	¥12,000	120	Flat (width) 12.7 x (thickness) 0.90	180	50	10	9.9
764-4973	TSF03-170	¥11,109	¥12,000	170	Flat (width) 12.7 x (thickness) 0.60	180	50	10	9.5
764-4957	TSF02-270	¥11,109	¥12,000	270	Flat (width) 12.7 x (thickness) 0.40	180	50	10	3.0
764-4965	TSF02-600	¥11,109	¥12,000	600	Flat (width) 12.7 x (thickness) 0.30	180	50	10	3.8
764-4949	TSF01-1200	¥11,109	¥12,000	1200	Flat (width) 12.7 x (thickness) 0.17	180	50	10	2.0

TRUSCO NAKAYAMA CORPORATION

Contact us: 0120-509-849 <http://www.orange-book.com/>

Minimo Stock **1,533** Items

Diamond File



- Features**
- A diamond file with carefully selected fine diamond abrasive grains electrodeposited.
 - Excellent in wear resistance, no shape change, and suitable for precision machining.
- Specs**
- Compatible materials: ceramics, glass, tool steel, alloy steel, carbide alloy, cermet, common steel, stainless steel, aluminum, copper
- Origin**
- Japan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Shape	Total Length (mm)	Blade Length (mm)	Width (mm)	Thickness (mm)	SPQ (piece)	Weight (g)
750-9669	RD5401	¥3,802	¥3,520	170	Flat	175	50	5.0	1.2±0.3	1	9
750-9677	RD5402	¥4,158	¥3,850	170	Flat	175	50	5.0	1.3±0.3	1	9
750-9685	RD5403	¥4,396	¥4,070	140	Flat	175	40	6.0	0.9±0.3	1	9
750-9693	RD5404	¥4,396	¥4,070	170	Flat	175	40	6.0	0.9±0.3	1	9
750-9707	RD5405	¥4,396	¥4,070	270	Flat	175	40	6.0	0.9±0.3	1	9
750-9715	RD5406	¥3,920	¥3,630	140	Flat	175	50	6.0	1.3±0.3	1	10
750-9723	RD5407	¥3,920	¥3,630	170	Flat	175	50	6.0	1.3±0.3	1	10
750-9731	RD5408	¥4,925	¥4,560	170	Flat	175	60	7.0	1.6±0.3	1	14
750-9740	RD5409	¥6,178	¥5,720	140	Flat	200	70	8.0	1.8±0.3	1	20
750-9758	RD5410	¥6,178	¥5,720	170	Flat	200	70	8.0	1.8±0.3	1	20
750-9766	RD5421	¥3,802	¥3,520	170	Flat taper	150	30	2.5	1.2±0.3	1	5
750-9774	RD5422	¥3,802	¥3,520	270	Flat taper	150	30	2.5	1.2±0.3	1	5
750-9782	RD5423	¥4,925	¥4,560	140	Flat taper	175	50	4.2	1.9±0.3	1	10
750-9791	RD5424	¥6,178	¥5,720	140	Flat taper	175	50	7.0	2.3±0.3	1	20
750-9804	RD5425	¥6,178	¥5,720	170	Flat taper	175	50	7.0	2.3±0.3	1	20
750-9812	RD5427	¥7,063	¥6,540	140	Flat taper	200	50	9.0	2.4±0.3	1	33
750-9821	RD5428	¥8,078	¥7,480	140	Flat taper	200	70	11.0	3.1±0.3	1	45
750-9901	RD5501	¥3,326	¥3,080	270	Round	175	40	1.1	1.1	1	58
750-9910	RD5502	¥3,326	¥3,080	600	Round	175	40	1.0	1.0	1	58
750-9928	RD5503	¥3,326	¥3,080	170	Round	175	50	2.2	2.2	1	5
750-9936	RD5504	¥3,143	¥2,910	170	Round	175	50	3.1	3.1	1	10
750-9944	RD5507	¥3,380	¥3,130	270	Round	180	60	3.5	3.5	1	13
750-9952	RD5508	¥4,158	¥3,850	170	Round	200	70	4.2	4.2	1	18
750-9961	RD5509	¥4,568	¥4,230	170	Round	200	50	5.6	5.6	1	31
750-9839	RD5442	¥3,326	¥3,080	170	Square	175	50	2.7	2.7	1	10
750-9847	RD5461	¥3,024	¥2,800	170	Half-round	175	40	4.8	1.6	1	7
750-9855	RD5462	¥3,143	¥2,910	170	Half-round	175	50	5.9	1.8	1	10
750-9863	RD5463	¥4,158	¥3,850	170	Half-round	175	60	6.8	2.1	1	13
750-9871	RD5491	¥3,143	¥2,910	170	Triangle	175	40	2.8	2.8	1	7
750-9880	RD5494	¥4,039	¥3,740	270	Triangle	180	60	4.3	4.3	1	12
750-9898	RD5495	¥4,158	¥3,850	170	Triangle	200	70	5.0	5	1	18
750-9979	RD5521	¥3,143	¥2,910	170	Oval	175	40	3.3	2	1	6
750-9987	RD5522	¥6,178	¥5,720	170	Oval	180	60	4.8	2.9	1	14
750-9995	RD5561	¥6,469	¥5,990	170	Double-ended riffler (flat)	148	18	2.0	3.2	1	10
751-0012	RD5564	¥6,469	¥5,990	170	Double-ended riffler (round)	148	18	2.6	2.6	1	7
751-0021	RD5566	¥6,944	¥6,430	170	Double-ended riffler (oval)	148	18	3.0	3.5	1	7

MINITOR Co.Ltd

Contact us: 03-3633-7181 <http://www.minitor.co.jp/>