

Angle Plates


Aluminum / Stainless Steel / Dimension Fixed

■ **Features:** Weight reduction is possible as opposed to cast iron.




Type	Hole Machining Selection	Material
AIK	FB (No Hole)	(W=60) AC4C-T5 (W=100) AC7A
	D (Through Holes)	
	K (Through Holes and Dowel Holes)	

■ **Hole Machining Selection FB (No Hole)**
AIKFB



Part Number	Type	H	A	W	T	T ₁	Unit Price	
No Hole AIKFB	60	60	60	60	10	10		
		70						
		80						
		90						
	100	50	100	15	14			
		60	60	10	10			
		100	100	15	14			
		150	70	100	15	14		
	200	100	100	15	14			
		120	100	15	14			
	250	120	100	18	15			
	300							
350	150	100	18	15				
400								


■ **Hole Machining Selection D (Through Holes)**
AIKD



Part Number	Type	H	A	Angle Plate Body			Through Hole					Unit Price	
				W	T	T ₁	d	B	X	F	Y		G
Through Holes AIKD	60	60	60	60	10	10	6.5	35	30	-	25	25	
		70									30	30	
		80									35	30	
		90									35	35	
	100	50	100	15	14	11	70	35	-	45			
		60	60	10	10	6.5	35	30	-	40	40		
		100	100	15	14	11	70	45	40	45			
		150	70	100	15	14	11	70	40	-	75	60	
	200	100	100	15	14	11	70	50	50	110	70		
		120	100	15	14	11	70	50	50	140	90		
	250	120	100	18	15	11	70	50	50	190	90		
	300									230	100		
350	150	100	18	15	11	70	40	90	260	120			
400													

ⓘ Portions without specific dimensions are same as AIKFB (No Hole Type).

■ **Hole Machining Selection K (Through Holes and Dowel Holes)**
AIKK



Part Number	Type	H	A	Angle Plate Body			Through Hole					Dowel Hole			Unit Price
				W	T	T ₁	d	B	X	F	Y	G	Dh7	a	
Through Holes and Dowel Holes AIKK	60	60	60	60	10	10	6.5	35	30	-	25	25	37.5		
		70									30	42.5			
		80									30	50			
		90									35	52.5			
	100	50	100	15	14	11	70	35	-	45	10	-	65		
		60	60	10	10	6.5	35	30	-	40	6	45	60		
		100	100	15	14	11	70	45	40	45	10	65	65		
		150	70	100	15	14	11	70	40	-	75	60	10	55	105
	200	100	100	15	14	11	70	45	40	45	10	65	65		
		120	100	15	14	11	70	50	50	110	70	10	75	145	
	250	120	100	18	15	11	70	50	50	140	90	10	75	185	
	300									190	90			235	
350	150	100	18	15	11	70	40	90	230	100	10	85	280		
400									260	120			320		

ⓘ Portions without specific dimensions are same as AIKFB (No Hole Type).

Ordering Example
Part Number - A
AIKFB70 - 60