


Neutralization Brushes / Conductive Copper Foil Tape / Neutralization Tapes

Neutralization Brushes



Type	Material	
	Holder	Brush
EBRS	A1050P	SUS304 (12μm)



When L≥201, there will be 3 holes 10mm away from both ends and on the center.


Part Number		L 1mm Increments	Unit Price				
Type	H		L50~100	L101~200	L201~300	L301~400	L401~500
EBRS	10	50~500					
	20						



Ordering Example
Part Number - L
EBRS10 - 500




Example




Static prone locations of transfer lines.

Conductive Copper Foil Tape



RoHS10

ECTP



Material Main Body: Copper
Adhesive: Conductive Adhesives

Features

- Usable in a wide range of applications to secure electroconductivity of equipments.
- Electroconductive adhesive with electric resistance of 160mΩ/4cm² is used.

Characteristic Value

Item	Unit	Value
Electric Resistance of Adhesive Layer	mΩ/4cm ²	160
Tensile Strength	N/cm	39.2
Adhesive Strength (for SUS 180 deg. Peeling Strength)	gf/20mm	700
Elongation	%	-

The above values are not guaranteed values but an example of measured values.

Part Number		L (Meter)	T(mm)	Unit Price 1 ~ 19 pc(s).	Volume Discount Rate 20~50
Type	W(mm)				
ECTP	50	10	0.08		

L dimension is in meters.

Peel off backing paper to adhere it to an object. Clean the mating surface off oil and dust.

Can be cut with a utility knife.



Ordering Example
Part Number
ECTP50


For orders larger than indicated quantity, please check with WOS.

Neutralization Tapes



RoHS10

Type	Material	
	ELTA	① Silver Plating Polyester Fiber



Part Number		L 1mm Increments	T	Unit Price				
Type	W			L20~100	L101~200	L201~300	L301~400	L401~500
ELTA	10	20~500	0.6					
	25							
	50							



Ordering Example
Part Number - L
ELTA10 - 500