



Fence Extrusions / Joint Brackets

C Extrusions




RoHS10




Material: A6063S-T5
Surface Treatment: Anodize

Part Number Type	No.	1mm L Increment	Mass kg/m	Sectional Area mm ²	Cross Sectional Moment of Inertia mm ⁴		Unit Price (Less than 300mm)	Unit Price/m (300mm or More)
					l _x	l _y		
HFSFES	30-3	50~4000	0.34	125	1074	9933		
	30-5		0.41	150	2035	10690		
	40-3		0.42	153	1430	22510		
	40-5		0.48	176	2656	23830		

H Extrusions



RoHS10



Material: A6063S-T5
Surface Treatment: Anodize

Part Number Type	No.	1mm L Increment	Mass kg/m	Sectional Area mm ²	Cross Sectional Moment of Inertia mm ⁴		Unit Price (Less than 300mm)	Unit Price/m (300mm or More)
					l _x	l _y		
HFSFEW	30-3	50~4000	0.395	145	1132	10040		
	30-5		0.476	175	2148	10160		
	40-3		0.51	188	1524	23770		
	40-5		0.64	235	2844	23890		

Ordering Example: Part Number - L
HFSFES30-3 - 1200

Alterations Specified hole machining is available.

Alterations Code	Counterboring					Through Hole					Unit Price					
	Z Selection			XA	XB	XC	XD	XE	D Selection	XA	XB	XC	XD	XE	One Counterbore Hole	1 Through Hole
Spec.	Z	d	d ₁	Distance from the Left End mm					ØD	Distance from the Left End mm						
Specifications of Hole Size and Position	5	5.5	9.5	7~(L-7)					3.5	7~(L-7)						
	6	6.5	11						4.5							
									5.5							
									6.5							

- Specified Hole Machining**
- Select hole type and size Z (for Counterbore) or D (for Through hole).
 - Specify the distance from the left end to holes XA, XB, XC, XD and XE in order.
 - Specify up to 5 counterbores or through holes. ☒ Combination of counterbore and through hole is not available.

Ordering Example: Part Number - L - Alterations
HFSFES30-3 - 150 - LCT45 - Z5 - XA45 - XB80 - XC120

Alteration Code	45° Cut ☑ Applicable to HFSFES only.	
	Left	Right
Spec.	LCT45	RCT45

