


Foot Bases

RoHS10

Type	M Material	S Surface Treatment
HLF, GLF	SS400	Trivalent Chromate
HLFS	SUS304	-

HLF5, 6, 8
GLF8

HLFS5, 6, 8 (Stainless Steel)



HLF and GLF Types have no plating finish on tapped holes.

Part Number	Type	Extrusion	Leveling Mount M	Shape	A	B	W	W1	V	E	T	Counterbore MA	Mass (kg)		Screw		HLF(GLF)		HLFS				
													HLF(GLF)	HLFS	Screw	Quantity	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate			
2040	HLF5 HLFS5	8	8	AA	20	40	20					9	5	0.05	M5-15	2							
2550		8		AA	25	50	25						12	8	0.07	M8-25							
2060		8		AC	20	60	20								0.06	M5-15							
2080		8		AC	20	80	60						9		0.1								
4040		8 10 12		AB	40		20								0.09		4						
404020		12		AE	40	20	10			15.5	14.5		12	5	0.08	M5-20	2						
404020A		12		AG	40	20	10								0.06			2					
4060		12		AJ	60	40	40	10		20					0.14	M5-15	4						
4080		12		AD	80	40	60					9			0.21								
3060		HLF6 HLFS6		10 12 16	16 20	AA	30	60	30							0.13	M8-25	2					
3090	12		AC	30		90	30								0.24								
30120	12		AA	120		90									0.31								
5050	10 12		AB	50			20								0.28								
50100	10 12		AD	100		50	70			20					0.42								
100100	16 20		AB	100									12	8	0.9				4				
6060	10 12 16		AB	60											0.28								
606030	12		AF	60		30	30			15	15				0.18				3				
606030A	12		AH	60		30	30								0.16				2				
6090	16		AD	90		60	60			30					0.47				4				
60120	16	AD	120	60	90								0.63										
4080*	HLF8 HLFS8	12 16	16 20	AA	40	80	40							0.31	M12-30	2							
40160		16			40	160	120										0.79						
4590*		16		AB	45	90	45								0.427								
45180		16 20		AD	180	135									0.94	M12-20	2						
50100*		16		AA	50	100	50								0.55								
8080		12 16 20		AB	80										0.73	M8-30	4						
808040		16		AF	80	40	40			20	20		16	12	0.38			M12-30	2				
808040A		16		AH	80	40	40								0.35		3						
80160		16 20		AD	160	80	120			40					1.56	M8-30	4						
9090		16 20		AB	90										0.95								
909045	16	AF	90	45	45			22.5	22.5				0.54	M12-20	3								
909045A	16	AH	90	45	45								0.51				2						
90180	16 20	AD	180	90	135			45					1.99	M8-30	4								
9090	GLF8	20	AB	90	45	50							0.95			M12-25	4						
100100				100	45	50									1.12			M12-20	4				

*Foot bases marked with * in the specification table are also applicable to high rigid aluminum extrusion.

Mounting screws are not included.

Ordering Example	Part Number	-	M
	HLF6-3060	-	10