

Multi Stage Two-Axis Platform




Spec

※ This drawing could be changed in order to improve the product without any notice.

Model No	P-25	P-25-T
Stage Surface (mm)	140×140×45	140×140×45
Center Hole	Solid	Thru
Stroke XY (mm)	±12.5	
Resolution (mm)	10um/division(0.01)	
Travel Guide	Round Bar & Ball Bush	
Material	Aluminum	
Load Capacity (kg) Center	10	10
Load Capacity (kg) Vertical	5	5
Weight (kg)	1	

P-25



P-25-T

