


Note that, for some of the types shown here, order might be unable to be received by the MISUMI Thailand, Malaysia, Indonesia, and/or India offices.

Caster Kits for Doors / Assembly Fixtures / Drilling Jigs / Repair Pen

Caster Kits for Doors

M Material: Plate: SS400 Trivalent Chromate
Caster: SPHC Trivalent Chromate
Rubber Wheel



Part Number		Extrusion	Caster Allowable Load N	Mass (g)	Unit Price	Volume Discount Rate
Type	No.				1 ~ 9 pc(s)	10~20
SQCM	6	30 Square	350	160		
	8	40 Square				


For orders larger than indicated quantity, please check with WOS.

No.	Plate				Dedicated Caster		Extrusion Mounting			
	B	W	T	d	D	H	Quantity	Mounting Screw	Nut	Quantity
6	30	15	6	7	50	68	1	SCB6-14	HNTF6-6	
8	40	20	6	8.5	50	68	1	SCB8-18	HNTF8-8	2

Ordering Example **Part Number**
SQCM6


Assembly Fixtures

RoHS 10



Part Number		Extrusion (Series)	Component			Unit Price	Volume Discount Rate			
Type	No.		① Plate	Quantity	② Wing Screw	Quantity	③ Post-Assembly Fitting Nut	Quantity	1-8 pc(s)	9-20
HFZG	5	HFS5	HPTSS5	1	CHOB4-8	2	HNTFSN5-4	2		
	6	HFS6	HPTSS6	1	CHOB6-12	2	HNTFSN6-6	2		
	8	HFS8	HPTSS8	1	CHOB8-15	2	HNTFSN8-8	2		
	8-45	HFS8-45	HPTSS8-45	1	CHOB8-15	2	HNTFSN8-8	2		

ex Example
Mount by straddling over two extrusions. By tightening the wing screw, the plane of the extrusion surface of (A) and (B) is made. Then (A) and (B) are connected with brackets.





Ordering Example **Part Number**
HFZG6

Drilling Jigs
Blind Joint D Hole / Wrench Hole Machining

RoHS 10


Main Body, Locating Plate
M Material: SS400
S Surface Treatment: Black Oxide



- 1) Attach the Locating Plate to one of the holes on the Drilling Fixture.
- 2) Slide a drilling fixture into the extrusion channel up to the Locating Plate.
- 3) Drill a hole using the positioning jig bushing.

Part Number		A	B	P	H	R	D	Extrusion (Series)	Component				Unit Price			
Type	No.								Clamp Lever	Quantity	Nut	Quantity		Screw	Quantity	Locating Plate
HFSJG	5	100	25	10	10	7.3	7.1	HFS5	CLDM5-20-Y	1	HNTTSN5-5	1	CHOB5-8	2	1 pc.	
	6	100	30	15	15	8	11.1	HFS6	CLDM6-20-M	1	HNTFSN6-6	1	CHOB5-8	2	1 pc.	
	8	110	40	20	20	8	13.1	HFS8	CLDM8-25-B	1	HNTFSN8-8	1	CHOB5-8	2	1 pc.	
	8-45	120	45	22.5	22.5	8	15.1	HFS8-45	CLDM8-25-S	1	HNTFSN8-8	1	CHOB5-8	2	1 pc.	

Applicable Extrusion Series	H mm	H1 mm	D Type Hole mm	M Type Hole mm	d (Wrench Hole) mm
HFS5	10	10	-	7.1	7.3
HFS6	15	15	11.1	11.1	8
HFS8	20	20	13.1	13.1	8
HFS8-45	22.5	20	15.1	13.1	8



Ordering Example **Part Number**
HFSJG6

Black Anodize Spot Repair Pen
ANCP

Part Number	Volume (ml)	Type	Features	Color	Usage	Operating Temp. Range (°C)	How to Use / Dry Condition	Main Component	Unit Price	Volume Discount Rate
ANCP	13	Pen	A felt-tipped pen that can quickly repair flaws on black anodized items. Repairs become less noticeable as the color is similar to that of black anodized aluminum extrusions.	Mat Black	Flaw repairs of black anodized type on aluminum extrusions. Marking on extrusions.	5~35	Shake well before use, and directly apply on the surface to repair.	Acrylic Resin	1 ~ 9 pc(s)	10~50

Ordering Example **Part Number**
ANCP