

**Standard**

Part Number	T	A	Unit Price				
			B300 400	B401 500	B501 600	B601 700	B701 800
ACAE (Transparent)	3	300-400	-	-	-	-	-
		401-500	-	-	-	-	-
		501-600	-	-	-	-	-
		601-700	-	-	-	-	-
		701-800	-	-	-	-	-
	5	801-900	-	-	-	-	-
		901-1000	-	-	-	-	-
		1001-1100	-	-	-	-	-
		300-400	-	-	-	-	-
		401-500	-	-	-	-	-
	8	501-600	-	-	-	-	-
		601-700	-	-	-	-	-
		701-800	-	-	-	-	-
		801-900	-	-	-	-	-
		901-1000	-	-	-	-	-
ACBAE (Brown Smoke)	3	1001-1100	-	-	-	-	-
		300-400	-	-	-	-	-
		401-500	-	-	-	-	-
		501-600	-	-	-	-	-
		601-700	-	-	-	-	-
	5	701-800	-	-	-	-	-
		801-900	-	-	-	-	-
		901-1000	-	-	-	-	-
		1001-1100	-	-	-	-	-
		300-400	-	-	-	-	-
	8	401-500	-	-	-	-	-
		501-600	-	-	-	-	-
		601-700	-	-	-	-	-
		701-800	-	-	-	-	-
		801-900	-	-	-	-	-

**Antistatic**


Part Number	T	A	Unit Price				
			B300 400	B401 500	B501 600	B601 700	B701 800
ACTAE (Transparent)	3	300-400	-	-	-	-	-
		401-500	-	-	-	-	-
		501-600	-	-	-	-	-
		601-700	-	-	-	-	-
		701-800	-	-	-	-	-
	5	801-900	-	-	-	-	-
		901-1000	-	-	-	-	-
		1001-1100	-	-	-	-	-
		300-400	-	-	-	-	-
		401-500	-	-	-	-	-
	8	501-600	-	-	-	-	-
		601-700	-	-	-	-	-
		701-800	-	-	-	-	-
		801-900	-	-	-	-	-
		901-1000	-	-	-	-	-
ACBAE (Brown Smoke)	3	1001-1100	-	-	-	-	-
		300-400	-	-	-	-	-
		401-500	-	-	-	-	-
		501-600	-	-	-	-	-
		601-700	-	-	-	-	-
	5	701-800	-	-	-	-	-
		801-900	-	-	-	-	-
		901-1000	-	-	-	-	-
		1001-1100	-	-	-	-	-
		300-400	-	-	-	-	-
	8	401-500	-	-	-	-	-
		501-600	-	-	-	-	-
		601-700	-	-	-	-	-
		701-800	-	-	-	-	-
		801-900	-	-	-	-	-

**Hole Machining Charge**

Pre-drilled Type	Screw Nominal		
	N (Through)	P (Countersink)	Q (Keyhole)
2H			
4H			
6H			
8H			


Pre-drilled Type Price = Standard Type Unit Price + Hole Machining Charge

(Ex.) Part Number - A - B - T - F - G - Screw Nominal Dia.  
 ACTAE4H - 500 - 400 - 5 - F240 - G160 - N8 >>  
 (Standard Type Unit Price) + (Hole Machining Charge) = Pre-Drilled Type Price



**ACALMG**  
(Acrylic, Transparent)  
**ACBLMG**  
(Acrylic, Smoke Brown)

Properties P949  
 Operating Ambient Temperature: -30 ~ 80°C



Part Number	Type	T	A	B	L	R*	S
			1mm Increment	1mm Increment	1mm Increment		
ACALMG ACBLMG		5	200~700	200~700	200~1000	140	137.5

\* Curved panels for R300 and R500 are not available.

Ordering Example  
 Part Number - A - B - L - R  
 ACALMG5 - A435 - B685 - L770 - R140

Part Number	Type	T	A	B	Unit Price						
					L						
					200-500	501-600	601-700	701-800	801-900	901-1000	
ACALMG ACBLMG	5		200-500	200-500							
				501-600							
			501-600	601-700							
				400-500							
			601-700	501-600							
				601-700							
			601-700	400-500							
				501-600							
			601-700	601-700							
				601-700							

