

## Specifications / 規格表

Type	型號/ Model	尺寸/ Dimensions	規格/ Datasheet
反射型 (Reflective)	FR-620-F Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 180mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0
	FR-620-M-H33 Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 180mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0
	FR-620-KS5 Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 180mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.
	FRX-620 Free cut		*Fiber Type : Long Sensing Range *Sensing distance(BR2/L999) : 240mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R40 *Fiber diameter : OD=Ø2.2 ID=Ø1.5
	FR-520 Free cut		*Fiber Type : Standard *Sensing distance(BR2/L999) : 180mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0
	FRC-520 Free cut		*Fiber Type : Coaxial *Sensing distance(BR2/L999) : 140mm *Operate temperature : -55°C~+70°C *Minimum bending radius : R25 *Fiber diameter : OD=Ø2.2 ID=Ø1.0x1/ Ø0.265x15

※ : M6 : Toothed Lock Washer Ø11  
Width Across Flats 10mm, Thickness 2.5mm