


Plastic Clamp Levers / Miniature Plastic Clamp Levers



| Type | Lever | Screw | | Spring |
|------|---------------------|------------|---------------------|------------|
| | M Material | M Material | S Surface Treatment | M Material |
| CLNP | Nylon 6 (Mat Black) | SUM22L | Black Oxide | SUS304-WPB |
| CLSP | | SUS303 | - | |

Threaded
CLNP
CLSP



Hex Socket B is created during a production of Levers. It is not a socket used during an installation of Levers.



| Part Number | Type | M | L Selection | | | | | | R | H | H ₁ | (h) | S | D | d | Number of Serrated Teeth | B | Max. Load F _{max} (N) | Max. Tightening Force P _{max} (kN) | Reference Mass (g) | Unit Price | |
|--------------|------|----|-------------|------|----|----|----|----|------|------|----------------|-----|----|----|----|--------------------------|-----|--------------------------------|---------------------------------------------|--------------------|------------|--|
| | | | CLNP | CLSP | | | | | | | | | | | | | | | | | | |
| CLNP CLSP | 4 | 12 | 16 | 20 | 25 | | | 48 | 34 | 36 | 25.5 | 3 | 13 | 10 | 16 | 3 | 21 | 1.7 | 18 | | | |
| | 5 | 12 | 16 | 20 | 25 | 32 | | | | | | | | | | 42 | 2.7 | | | | | |
| | 6 | 12 | 16 | 20 | 25 | 32 | 40 | | | | | | | | | 70 | 3.8 | 20 | | | | |
| | 8 | 16 | 20 | 25 | 32 | 40 | 50 | 65 | 44.5 | 46.5 | 31 | 4 | 18 | 14 | 20 | 4 | 120 | 7 | 40 | | | |
| | 10 | | 20 | 25 | 32 | 40 | 50 | 82 | 54 | 56 | 35 | 6.5 | 21 | 16 | 24 | 4 | 200 | 11 | 80 | | | |
| | 12 | | 25 | 32 | 40 | 50 | | 92 | 64 | 66 | 42 | 6.5 | 25 | 19 | 28 | 5 | 290 | 16 | 120 | | | |



| Type | Lever | Screw | | Spring |
|------|---------------------|------------|-------------|---------------------|
| | | M Material | M Material | S Surface Treatment |
| LNP | Nylon 6 (Mat Black) | SUM22L | Black Oxide | SUS304-WPB |

Threaded
LNP

Tapped
LNF




Hex Socket B is created during a production of Levers. It is not a socket used during an installation of Levers.

| Part Number | Type | M | L Selection | | | | | | R | H | H ₁ | (h) | S | D | d | Number of Serrated Teeth | B | Max. Load F _{max} (N) | Max. Tightening Force P _{max} (kN) | Reference Mass (g) | | Unit Price | |
|----------------------------|------|----|-------------|-----|----------|--------|-----|-----|------|------|----------------|-----|-----|------|------|--------------------------|-----|--------------------------------|---------------------------------------------|--------------------|----|------------|--|
| | | | LNP | LNF | Threaded | Tapped | LNP | LNF | | | | | | | | | | | | | | | |
| Threaded LNP Tapped LNF | 4 | 12 | 16 | 20 | 25 | | | 45 | 35.5 | 39 | 24.5 | 4.2 | 13 | 10 | 18 | 3 | 21 | 1.7 | 18 | 16 | | | |
| | 5 | 12 | 16 | 20 | 25 | 32 | | | | | | | | | | 42 | 2.7 | | | | | | |
| | 6 | 12 | 16 | 20 | 25 | 32 | 40 | | | | | | | | | 70 | 3.8 | 20 | 14 | | | | |
| | 8 | 16 | 20 | 25 | 32 | 40 | 50 | 10 | 63 | 46.3 | 50.3 | 31 | 6.5 | 17.5 | 13.5 | 24 | 4 | 120 | 7 | 40 | 30 | | |
| | 10 | | 20 | 25 | 32 | 40 | 50 | 14 | 78 | 55.4 | 59.4 | 36 | 8 | 21 | 16 | 26 | 4 | 200 | 11 | 80 | 50 | | |
| | 12 | | 25 | 32 | 40 | 50 | | 17 | 92 | 66 | 70 | 43 | 11 | 25 | 19 | 28 | 5 | 290 | 16 | 120 | 70 | | |



| Type | Lever | Screw | | Spring |
|-------|---------------------|------------|---------------------|------------|
| | M Material | M Material | S Surface Treatment | M Material |
| CLNPC | Nylon 6 (Mat Black) | SUM22L | Black Oxide | SUS304-WPB |

Threaded
CLNPC



* This hex socket is created during a production of Levers. It is not a socket used during an installation of Levers.

| Part Number | Type | M | L Selection | | | | Number of Serrated Teeth | Max. Load F _{max} (N) | Max. Tightening Force P _{max} (kN) | Reference Mass (g) | Unit Price |
|----------------|------|----|-------------|----|----|----|--------------------------|--------------------------------|---------------------------------------------|--------------------|------------|
| | | | CLNPC | | | | | | | | |
| Threaded CLNPC | 4 | 12 | 16 | 20 | 25 | 16 | 21 | 1.7 | 18 | | |
| | 5 | 12 | 16 | 20 | 25 | | 42 | 2.7 | | | |
| | 6 | 12 | 16 | 20 | 25 | | 32 | 70 | | | 3.8 |

Ordering Example

| Part Number | L |
|-------------|----|
| CLNP4 | 12 |
| LNP8 | 20 |
| LNF10 | 14 |
| CLNPC4 | 12 |