


Pull Handles - Non-Metal / T-Shaped



Nylon Type

RoHS10

UPFN

		M Material	
Handle		Glass Fiber Reinforced Nylon 6	
Thread		Brass (Insert)	

Part Number Type	A	L	Handle Color	L ₁	H	h	M (Coarse)	Allowable Load (N)	Mass (g)	Unit Price			
										B (Black)	W (White)	M (Orange)	R (Red)
UPFN	26	105	B (Black)	121	37	29	6	500	55				
		110	W (White)	133	40	32							
		117	M (Orange) R (Red)										

⚠ The default handle color is black unless specified.

Ordering Example: **UPFN26** - **L105** - **B**

For Panels

RoHS10

**HHDS
HHDSW
HHDSA
HHDS**

Type	M Material	S Surface Treatment
HHDS	Polycarbonate (Black)	-
HHDSW	Polycarbonate (White)	-
HHDSA	ADC12	Baked Paint: Silver Metallic
HHDS	SUS304 Equivalent	Buffing

Part Number Type	L	L ₁	H	h	A	Mass (g)				Unit Price			
						HHDS, HHDSW	HHDSA	HHDS		HHDS	HHDSW	HHDSA	HHDS
HHDS	90	110	32	24	13	17	43	90					
HHDSW	104	127	37	27.7	16	25	65	150					
HHDSA	122	149	43.3	32.5	19	42	102	220					

⚠ There is no allowable load for the panel mounting handles.

Rubber Type

UGFN

		M Material	
Handle		EPDM Rubber (Mat Black)	
Thread		Brass (Insert)	

Part Number Type	L	L ₁	Mass (g)	Unit Price
UGFN (Rubber Type)	40	50	10	
	53	63	12	
	70	80	15	

⚠ The allowable load value not provided since unfeasible to measure.

T-Shaped

TSPF

* There is a 0.2 mm protrusion to prevent loosening.

		M Material		S Surface Treatment	
Handle		Glass Fiber Reinforced Nylon (Mat Black)		-	
Thread		SS400 (Insert)		Trivalent Chromate	

Part Number Type	D	M	Lf	d	Mass (g)		Unit Price	
TSPF	50	3	20	11	26			
		4			28			
		5			30			
		5			46			
	80	6	25	16	50			
		6			56			
		8						
		8						

Ordering Example: **HHDS90** - **M**
UGFN70 - **M**
TSPF50 - **4**