


Stainless Steel Pipes / Stainless Steel Pipe Fittings



Type	Material	Standards	Annealing	Gloss
SKHR	SUS304	JIS G3459	Atmospheric Annealing	Not provided
SKH			Bright Annealing (BA Pipe)	Provided
SKER	SUS316	JIS G3459	Atmospheric Annealing	Not provided
SKE			Bright Annealing (BA Pipe)	Provided

This product is a seamless pipe.





Values in () are for t dimension of SKH.

D	t
4	1
6	1
6.35 (1/4 inch)	1
8	1 (1.2)
9.53 (3/8 inch)	1
10	1 (1.5)
12	1 (1.5)
12.7 (1/2 inch)	1
16	1

Part Number	Type	D	L 1mm Increment	Unit Price														
				SKHR				SKH				SKER				SKE		
				L20-100	L101-200	L201-300	L301-400	L401-500	L20-100	L101-200	L201-300	L301-400	L401-500	L20-100	L101-200	L201-300	L301-400	L401-500
SKHR SKH SKER SKE	4	4	20-500															
	6	6																
	6.35 (1/4 inch)	6.35																
	8	8																
	9.53 (3/8 inch)	9.53																
	10	10																
	12	12																
	12.7 (1/2 inch)	12.7																
	16	16																

Ordering Example: Part Number - L
SKE10 - 300

For tightening procedure and structure of fittings, and applicable pipe specification, refer to P1300.



Part Number	Type	D	R (PT) Selection	T R(PT)	L	E	F	l	Square		Unit Price	Volume Discount Rate
									Main Body H	Nut H		
SKTGK	3.18 (1/8)	1	1/8	32.9	2.5	13.4	26	12	12			
			1/4	34.9	2.5	13.4	28	14	12			
	4	1	1/8	35.8	3.5	15.3	28.5	14	14			
			1/4	37.8	3.5	15.3	30.5	14	14			
	6	1	1/8	35.9	5	15.4	28.5	14	14			
			1/4	37.9	5	15.4	30.5	14	14			
			3/8	38.9	5	15.4	31.5	17	14			
			1/2	44.4	5	15.4	37	22	14			
	6.35 (1/4)	1	1/8	35.9	5	15.4	28.5	14	14			
			1/4	37.9	5	15.4	30.5	14	14			
	8	1	1/8	36.8	5	16.8	29	14	15.9			
			1/4	38.8	6	16.8	31	14	15.9			
			3/8	39.8	6	16.8	32	17	15.9			
			1/2	45.3	6	16.8	37.5	22	15.9			
	9.53 (3/8)	1	1/4	39.8	7	17.8	32	17	19			
			3/8	40.8	7.5	17.8	33	17	19			
			1/2	46.3	7.5	17.8	38.5	22	19			
			3/4	49.3	10	22.8	38.5	22	23			
	10	1	1/4	39.8	7	17.8	32	17	19			
			3/8	40.8	8	17.8	33	17	19			
			1/2	46.3	8	17.8	38.5	22	19			
			3/4	49.3	10	22.8	38.5	22	23			
	12	1	1/4	42.8	7	22.8	32	22	23			
			3/8	43.8	9	22.8	33	22	23			
1/2			49.3	10	22.8	38.5	22	23				
3/4			52.3	12	28.8	38.5	22	23				
12.7 (1/2)	1	1/4	42.8	7	22.8	32	22	23				
		3/8	43.8	9	22.8	33	22	23				
		1/2	49.3	10	22.8	38.5	22	23				
		3/4	52.3	12	28.8	38.5	22	23				

L and F are dimensions for hand tightening.
Values in () for D dimension are by inch.

Part Number	Type	D	R (PT) Selection	T R(PT)	L	L1	E	E1	F	l	Square		Unit Price	Volume Discount Rate
											Main Body H	Nut H		
SKTGLK	3.18 (1/8)	1	1/8	24.9	22	2.5	5	13.4	18	12	12			
			1/4	25.9	24	2.5	5	13.4	19	14	12			
	4	1	1/8	27.8	22	3.5	5	15.3	20.5	14	14			
			1/4	27.8	24	3.5	5	15.3	20.5	14	14			
	6	1	1/8	27.9	22	5	5	15.4	20.5	14	14			
			1/4	27.9	24	5	5	15.4	20.5	14	14			
			3/8	28.9	27	5	5	15.4	21.5	17	14			
			1/2	30.9	35	5	5	15.4	23.5	22	14			
	6.35 (1/4)	1	1/8	27.9	22	5	5	15.4	20.5	14	14			
			1/4	27.9	24	5	5	15.4	20.5	14	14			
	8	1	1/8	28.8	22	5	5	16.8	21	14	15.9			
			1/4	28.8	24	6	6	16.8	21	14	15.9			
			3/8	29.8	27	6	6	16.8	22	17	15.9			
			1/2	31.8	35	6	6	16.8	24	22	15.9			
	9.53 (3/8)	1	1/4	30.8	27	7.5	7	17.8	23	17	19			
			3/8	30.8	27	7.5	8	17.8	23	17	19			
			1/2	32.8	35	7.5	8	17.8	25	22	19			
			3/4	35.8	43	10	10	22.8	25	22	23			
	10	1	1/4	30.8	27	7	7	17.8	23	17	19			
			3/8	30.8	27	8	8	17.8	23	17	19			
			1/2	32.8	35	8	8	17.8	25	22	19			
			3/4	35.8	43	10	10	22.8	25	22	23			
	12	1	1/4	35.8	28	7	7	22.8	25	22	23			
			3/8	35.8	30	9	9	22.8	25	22	23			
1/2			35.8	35	10	10	22.8	25	22	23				
3/4			38.8	43	12	12	28.8	25	22	23				
12.7 (1/2)	1	1/4	35.1	28	10	7	22.8	25	22	23				
		3/8	35.1	30	10	9	22.8	25	22	23				
		1/2	35.1	35	10	10	22.8	25	22	23				
		3/4	38.1	43	12	12	28.8	25	22	23				

L and F are dimensions for hand tightening.
Values in () for D dimension are by inch.

Ordering Example: Part Number - T
SKTGK6 - 3
SKTGLK9.53 - 4