

## WRG-AC Type


Examples of model number formation

WRG 3 - 125 AC H - 17Z

1 2 3 4 5 6

- 1 Part No. 2 Roller Size 3 Length of Race rail  
 4 Anti-Creep  
 5 Accuracy : Normal(No symbol), High(H), Precision(P)  
 6 The number of Roller

\* Please inquire us for your specially required dimensions & applicaton



Part No.	Max. Stroke	D	No. of Roller Z	Dimensions					
				L	A	B	C	M×P	N
WRG 2030 AC	18	2	4	30	12	6	5.4	1×15	7.5
WRG 2045 AC	24		7	45				2×15	
WRG 2060 AC	30		10	60				3×15	
WRG 2075 AC	44		12	75				4×15	
WRG 2090 AC	50		15	90				5×15	
WRG 2105 AC	64		17	105				6×15	
WRG 2120 AC	70		20	120				7×15	
WRG 2135 AC	84		22	135				8×15	
WRG 2150 AC	90		25	150				9×15	
WRG 2165 AC	96		28	165				10×15	
WRG 2180 AC	102	31	180	11×15					
WRG 3050 AC	28	3	7	50	18	8	8.3	1×25	12.5
WRG 3075 AC	48		10	75				2×25	
WRG 3100 AC	58		14	100				3×25	
WRG 3125 AC	78		17	125				4×25	
WRG 3150 AC	88		21	150				5×25	
WRG 3175 AC	108		24	175				6×25	
WRG 3200 AC	118		28	200				7×25	
WRG 3225 AC	138		31	225				8×25	
WRG 3250 AC	148		35	250				9×25	
WRG 3275 AC	168		38	275				10×25	
WRG 3300 AC	178		42	300				11×25	
WRG 3325 AC	198		45	325				12×25	
WRG 3350 AC	208		49	350				13×25	
WRG 4080 AC	58	4	7	80	22	11	10.2	1×40	20
WRG 4120 AC	82		11	120				2×40	
WRG 4160 AC	106		15	160				3×40	
WRG 4200 AC	130		19	200				4×40	
WRG 4240 AC	154		23	240				5×40	
WRG 4280 AC	178		27	280				6×40	
WRG 4320 AC	202		31	320				7×40	
WRG 4360 AC	226		35	360				8×40	
WRG 4400 AC	250		39	400				9×40	
WRG 4440 AC	274		43	440				10×40	
WRG 4480 AC	298		47	480				11×40	

Note 1) 1Set = 4 Race rail + 2 Roller cages + 8 Stoppers.

2) Basic load ratings are based and mass on 1 set.

3) Needed stopper additional indication is required.