


Cam Followers


Hex Socket on Head / Thread (Flat Type with Grease Fitting)



Application	Type		Material	Accessory
	With Seal	No Seal		
General	CFFH	CFAH	SUJ2	1 Hex Nut (S45C Carbon Steel, Black Oxide)
Low Dust Generation	CFFSH	CFASH	SUS440C Equivalent	Hex Nut 1 pc. (SUS304)
Heavy Load	CFFGH	-	SUJ2	1 Hex Nut (S45C Carbon Steel, Black Oxide)



D	Tolerance
30	0 -0.009
32-47	0 -0.011
52-80	0 -0.013
80-90	0 -0.015



RoHS 10

Operating Temp.: 80°C or lower

Part Number	Type	dh7 Tolerance	D (Selectable)	MxPitch	B	B1	L	d1	l	l1	r	f (Min.)	H	Mass (g)	Max. Tightening Torque (N • cm)	Unit Price						
																CFFH	CFFSH	CFFCH	CFFGH	CFAH	CFASH	
(With Seal) CFFH CFFSH CFFCH CFFGH	12	0 -0.018	30	12x1.5	14	15	40	3	14	6	1.5	20	6	105(107)	29.4							
			32											115(117)								
	16	0 -0.018	35	16x1.5	18	19.5	52	3	18	8	1.5	24	6	205(207)	70.6							
			40											295(300)		98						
	20	0 -0.021	47	20x1.5	24	25.5	66	3	22	9	1.5	36	6	450(455)	137							
			52											525(530)								
	(No Seal) CFAH CFASH	24	0 -0.021	62	24x1.5	29	30.5	80	4	25	11	1.5	40	8	915(925)	245						
				72											1150(1160)							
	30	0 -0.021	80	30x1.5	35	37	100	4	32	15	2	1.5	46	8	1880(1890)	480						
			85												1950(1960)							
				90											2000(2010)							

For the performance of Cam Followers, see Table 1 on P.1043.



Ordering Example
Part Number - D
CFFH20 - 52

Part Number Substitution Table for Cam Follower Standard Changes (D30-40,52 only)

Type	Old Part Number (D30-40,52)			New Part Number
	Old Standard	Old Hex Socket Type	Old Hex Socket on Thread	Hex Socket on Head and Thread
Cam Followers	CFUR	CFUA	CFUB	CFUH
	CFURS	CFUAS	-	CFUSH
	CFURC	CFUAC	-	CFUCH
	-	CFUAG	-	CFUGH
	CFU	CUA	-	CUH
	CFUS	CUAS	-	CUSH
	CFFR	CFFA	CFFB	CFFH
	CFFRS	CFFAS	-	CFFSH
	CFFRC	CFFAC	-	CFFCH
	-	CFFAG	-	CFFGH
	CFR	CFA	-	CFAH
	CFRS	CFAS	-	CFASH