

Guide Rails and Brackets


L Type

L-Shaped Conveyor Guide Rails



RoHS 10

CGL



Material: SUS304

Part Number	L		Unit Price
	5mm Increment		
CGL	150~ 300		
	305~ 500		
	505~ 750		
	755~ 1000		



Ordering Example
Part Number - L
CGL - 380

L-Shaped Conveyor Guide Rail Brackets - Standard Type



RoHS 10




CGK

(W=50,60)




CGKL

(W=100)




No.55



No.80



No.70



Ⓢ NO.55 ~ 80 have different bolt size for the conveyor mount part. Select an appropriate bolt according to the conveyor you are using.

Material: SUS304

Part Number		W	Unit Price
Type	No.		
CGK (W=50,60)	55	50	
	70	60	
	80		
CGKL (W=100)	55	100	
	70		
	80		



Alterations



Part Number

Type No. - (CL)
CGK 70 - CL



Ordering Example

Part Number

Type No.
CGK 80

Alterations	Code	Spec.
<p>Change to Product with Clamp Lever</p>	CL	<p>Hex socket set screws are replaced with the clamp lever (Orange, CLDMC4-8-M equivalent). Ⓢ Not applicable to CGK55/CGKL55</p>