


# Mini Rods



RoHS 10

Type	D Tolerance	M Material	H Hardness	S Surface Treatment
MRS	0 -0.005	SKH51	58HRC~	-
MRSB				Black Oxide
MRSM		SUJ2	-	Electroless Nickel Plating
MRSK				-
MRSD		SKD11	60HRC~	-
MRSS		SUS440C	56HRC~	-
MRSG		SUS304	-	-
MRSF		P/M High-Speed Steel	65~68HRC	-
MRSC		C3604 (Brass with Low Cadmium)	-	-




Discoloration may occur on rod ends.

Part Number Type	D	L 0.1mm Increment	Unit Price														
			MRS	MRSB	MRSM	MRSK	MRSD	MRSS	MRSG	MRSF	MRSC						
MRS MRSB MRSM MRSK MRSD MRSS MRSG MRSF MRSC	0.5	5.0~50.0															
	0.6																
	0.7																
	0.8																
	0.9																
	1.0		5.0~60.0														
	1.1																
	1.2																
	1.3																
	1.4																
	1.5																
	1.6																
	1.7																
	1.8		5.0~80.0														
	1.9																
	2.0																
	2.1																
	2.2																
	2.3		5.0~100.0														
	2.4																
	2.5																
	2.6																
	2.7																
	2.8																
	2.9		5.0~150.0														
	3.0																
	3.1																
	3.2																
	3.3																
	3.4																
3.5																	
3.6																	
3.7																	
3.8																	
3.9																	
4.0																	
4.1																	
4.2																	
4.3																	
4.4																	
4.5																	
4.6																	
4.7																	
4.8																	
4.9																	
5.0																	

Ordering Example: Part Number - L  
MRS1.2 - 60.0

Example



Alterations Example: Part Number - L - (AC)  
MRS1.2 - 60.0 - AC1.0

Alteration	Code	Spec.
Point Taper 	AC	Adds a 15° taper on the point. AC = 0.1mm Increment 0.5 ≤ AC ≤ 10 D - 2(AC tan 15°) ≥ 0.2 One end only is tapered.