


Chloroprene / Non-Staining Chloroprene Rubber Sheets


Chloroprene rubber excels in mechanical strength and alkali resistance. Non-staining chloroprene rubber which minimizes contamination from contacting materials is also available.
 For Rubber Gaskets, see P455. For Rubber Blocks, see P422.



A Selectable Type		A, B Configurable Type		Material	Hardness	Color
No Adhesive	Adhesive	No Adhesive	Adhesive			
RBCM	RBCMA	RBCMF	RBCMFA	Chloroprene Rubber (CR)	Shore A65	Black
RBOM	RBOMA	RBOMF	RBOMFA	Non-Staining Chloroprene Rubber (CR)	Shore A60	Gray
RBCW	RBCWA	RBCWF	RBCWFA	Chloroprene Rubber (CR)	Shore A60	White

Adhesive thickness is 0.14 ~ 0.2mm.
 For Adhesive Strength Data, see P438 (ADTR).
 Temperature limit for seals is 80°C.


Square Type



Band Type




A, B Configurable - Standard Type




Accuracy Standards

T Tolerance	A, B Tolerance
T	A, B
0.5 ±0.2	200 or Less ±0.5
1~3 ±0.3	201~300 ±1.0
5 ±0.4	301~500 ±1.5
10 ±0.6	
15~30 +2.0 -0.5	

Hole Machining Details



A, B Configurable - Hole Type



For Adhesive Type T5 or more, the adhesive tape may tear from the body. Please use it as temporary fixing, or in combination with bolt fixing.
 A, B dimension tolerance has been changed. Please refer to the accuracy standards above.

Square Type

Part Number		T	A Selection
Type	Type		
No Adhesive	Adhesive	1	300
		2	
		3	
		5	500
		10	
		15	
		20	T15 or more of RBOM and RBOMA, 300 Only
		30	

Band Type

Part Number		T	A Selection
Type	Type		
No Adhesive	Adhesive	1	3
			5
			10
			20
			30
			40
		5	50
		3	80
		10	100

A, B Configurable - Standard Type

Part Number		T	1mm Increment	
Type	Type		A	B
No Adhesive	Adhesive	1	10~500	10~500
		2		
		3		
		5		
		10		
		15		
		20	T15 or more of RBOMF and RBOMFA, 10~300 Only	
		30		

T dimension 15 is not available for RBCM and RBCWA.

L dimension is 500mm.

A ≥ B ≥ T

T dimension 15 is not available for RBCWF and RBCWFA.

A, B Configurable - Hole Type

Part Number		Nominal	T	1mm Increment (A ≥ B ≥ T)		0.5mm Increment	Screw Nominal Dia. Selection
Type	Type			A	B		
No Adhesive	Adhesive	1H	1	25~500	25~500	5~495 (1H Type)	3
		2H	2				4
		3H	3				5
		4H	5				6
		4H	10				8
		4H	15				10
		20	T15 or more of RBOMF and RBOMFA, 25~300 Only	T15 or more of RBOMF and RBOMFA, 25~300 Only	9~245 (3H, 6H Types)	3	
		30				4	

A ≥ B ≥ T

Dimension F Specification Range: For 1H, 2H, 3H: d(d1)+2.5 ≤ F ≤ A-d(d1)/2-2.5, for 2H, 4H: d(d1)+5 ≤ F ≤ A-d(d1)/5, for 3H, 6H: d(d1)+5 ≤ F ≤ A/2-d(d1)/2-2.5.

Dimension G Specification Range: For 1H, 2H, 3H: d(d1)+2.5 ≤ G ≤ B-d(d1)/2-2.5, for 4H, 6H: d(d1)+5 ≤ G ≤ B-d(d1)/5, (d for through holes, d1 for counterbored holes.)



Ordering Example

Part Number - A
 RBCM5 - 100
 RBOM10 - 500

A, B Configurable - Standard / Hole Type

Part Number - A - B - F - G - Screw Nominal Dia.
 RBCMF10 - 110 - 65
 RBCMF4H20 - 200 - 150 - F140 - G100 - Z5