

# Casters with Leveling Mounts

Light Load / Integrated Medium Load

## Light Load



RoHS10

Type	Main Body		Wheel	Leveling Mount	Bearing	
	M Material	S Surface Treatment	M Material	M Material	S Surface Treatment	Swiveling Part
<b>CMAF</b>	SPHC	Black Chromate	Phenol	Neoprene Rubber	Incorporated	Incorporated

### How to Lock Caster Swiveling



- Turn the nut ① marked up until it contacts the upper plate.
- After step ①, insert pins from the upper side of the plate to lock caster swiveling.

### Installation Method

- Lower the adjustment bolt to a desired height.
- Turn the nut ① up and fix the location.  
(Recommended Pin Dia.)

D50 06 O.A.L. 20  
65 08 O.A.L. 25  
75 08 O.A.L. 35

Ⓜ The pin is not included.



Part Number		Wheel Material	B	H	F	A	S1	S2	d1	d2	t	E1	E2	r1	r2	Allowable Load (N)	Unit Price
Type	D																
<b>CMAF</b>	50	F (Phenol)	28	68	110	90	5	5	8.5	6.2	2.3	25	35	53	61	1500	
	65		36	92	144	125	10	10	10.5	8.2	3.2	25	49	61	75	2000	
	75		36	106									28	69	75	2100	






Ordering Example Part Number - Wheel Material  
CMAF65 - F

## Integrated Medium Load



RoHS10

Type	Main Body		Wheel	Leveling Mount		Bearing	
	M Material	S Surface Treatment	M Material	M Material	S Surface Treatment	Swiveling Part	Wheel
<b>CMAS</b>	SPHC	Trivalent Chromate	Reinforced Nylon	SS400	Trivalent Chromate	Incorporated	Incorporated
<b>CMASS</b>	SUS304	-		SUS304	-		



Part Number		Wheel Material	H	ℓ	d	E	r	Allowable Load (N)	Unit Price	
Type	D								CMAS	CMASS
<b>CMAS</b> <b>CMASS</b>	50	F (Reinforced Nylon)	74	19.6	11	46	73	2500		
	65		95	18.8		51	84			



Ordering Example Part Number - Wheel Material  
CMAS65 - F