

# Leveler Bolts / Seating Plates - Standard

Round / Square / Thick

**Tip Sphere Hex Chamfered**

**Fine**

Type	Material	Hardness (Tip Induction Hardened)	Surface Treatment
L Fixed FJKMR	-	S45C	50~56HRC Trivalent Chromate

Part Number	Type	M (xP)	L	d	R	l	B	Load Capacity (kN)	Mass (g)	Unit Price
<b>FJKMR</b>		16 (x1.5)	100	14	7	10	13	44.0	150	
		20 (x1.5)		18	9		16	68.6	250	
		24 (x1.5)		20	10		18	98.8	300	

**Tip Sphere Head Cap**

**Fine**

Type	Material	Hardness (Tip Induction Hardened)	Surface Treatment
L Fixed FJKMB	-	S45C	50~56HRC Trivalent Chromate

Part Number	Type	M (xP)	L	d	R	l	B	Load Capacity (kN)	Mass (g)	Unit Price
<b>FJKMB</b>		16 (x1.5)	100	14	7	10	21	44.0	150	
		20 (x1.5)		18	9		24	68.6	250	
		24 (x1.5)		20	10		27	98.8	300	

**Tip SR Head Cap**

**Coarse**

**EX** Example Leveler Bolts  
SEPLC(P1126)

Type	Material	Hardness (Tip Induction Hardened)	Surface Treatment
L Fixed FJKBA	-	S45C	50~56HRC Trivalent Chromate

Part Number	Type	M (xP)	L	d	SR	B1	B2	E	F	T	Load Capacity (kN)	Mass (g)	Unit Price
<b>FJKBA</b>		12 (x1.75)	80 100	9	10	18	18.7	1	9.8	7.1	100		
		16 (x2.0)	100 120	13	12	21	23.7	6	12.5	9.8	200		
		20 (x2.5)		16	17	24	29.4		15.6	21.0	300		

**Ordering Example**

Part Number	-	L
FJKMR20	-	100
FJKMB24	-	103
FJKBA12	-	80

**Seating Plates**

**RoHS10**

**SEPLC**

**SEPLB**

**SEPFC**

**M** Material: FC250 **S** Surface Treatment: Paint (Blue)

Part Number	Type	D	T	Reference Load Capacity kN	Mass (g)	Unit Price
<b>SEPLC</b>	60	20	5.6	360		
		30	14.8	560		
		20	5.6	600		
	80	30	14.8	990		
		50	46.2	1720		
		20	5.6	950		
100	30	14.8	1560			
	50	46.2	2680			

Part Number	Type	D	T	Reference Load Capacity kN	Mass (g)	Unit Price
<b>SEPLB</b>	80	20	10.8	880		
		30	24.5	1310		
		50	68.5	2260		
	100	20	10.8	1350		
		30	24.5	2050		
		50	68.6	3400		
150	20	10.8	3210			
	30	24.5	4620			

Part Number	Type	D	T	K	d	W	h	Reference Load Capacity kN	Mass (g)	Unit Price
<b>SEPFC</b>	80	60	30	40	60	30	10	1650		
		100	80	40	70	38	12	3250		
		120	100	42	70	70	12	6450		
	150	150	150	42	70	80	20	12900		

**Ordering Example**

Part Number	-	T
SEPLC60	-	20
SEPLB80	-	30
SEPFC100	-	80

**EX** Example

Combination of these app. examples can be selected on our website.

Selection Detail **P87**

\*Enter the search keyword in the search box on e-Catalog. The search result will be shown in "Modular Assembler" area.

e-Catalog Search Keyword

#MA212 Search

