


# Manifold App. Example / Shape / Port Position Chart

Standard Position of the Mounting Hole



\*Standard mounting holes are located as shown in the drawing on the left. This is not applied for some types. For details, see each product page.

## App. Example

Material	Steel (SS400 Equivalent)	Stainless Steel (SUS304 Equivalent)	Aluminum Alloy
Recommended fluids	Lubricant, Cutting Oil, Coolant, etc. * It can also be used in air	Water, etc. * It can also be used in oil and air	Air, etc.
Features	Low Price	Rust resistant	Light
Max. Operating Pressure	20.6MPa≈210kgf/cm <sup>2</sup> or less		1MPa≈10kgf/cm <sup>2</sup> or less
App. Example	<p>Bifurcation of cutting oil</p>	<p>In combination with pressure gauge</p>	<p>Bifurcation of draining air</p>

## Manifold Blocks, Terminal Blocks

Page	P.1226, 1231, 1232	P.1227, 1230, 1233, 1234	P.1228, 1235, 1236	P.1229, 1237, 1238
Port Positions				
Page	P.1230, 1240	P.1239, 1251, 1252	P.1243	P.1243
Port Positions				
Page	P.1241	P.1242	P.1242	P.1243
Port Positions				
Page	P.1244	P.1244	P.1245, 1247, 1248	P.1246, 1249, 1250
Port Positions				

## Pipe Manifolds

Page	P.1256	P.1256	P.1257, 1258, 1259	P.1260	P.1260
Port Positions					