

Hinge Bases



L-Shaped Fulcrum Type

Features: Prevent interference by shifting Fulcrum.



Type		Material	Surface Treatment
U-Shaped	T-Shaped		
HGLTB	HGLNB	S45C	Black Oxide
HGLTM	HGLNM	Equivalent	Electroless Nickel Plating
HGLTS	-	SUS304	-

25 / (√6.3 / √1.6)



RoHS10

Part Number Type	DH7	W		H				B	S	T	d2	d1	H1	
		1mm Increment	5mm Increment	A	F	P	X							
U-Shaped HGLTB HGLTM HGLTS	3	3~6	15~25	20	10	-	14.5	H+5	8	9	4.5	8	4.5	
	4	4~8	20~30	22	11	-	15.5		10					
	5	5~10		25~35	25	12	-	18.5	H+8	12	16	5.5	9.5	5.5
	6	6~12	32		20	-	24	12						
	8	8~16	30~40	38	25	-	27	H+10	14	19	6.5	11	6.5	
	10	10~18		45	28	12	25		15					
	T-Shaped HGLNB HGLNM	12	12~30	35~45	50	34	14	28	H+12	15	22	6.5	11	6.5
		13	13~30							19				
		14	14~24	40~50	60	40	17	33	H+14	18	25	9	14	9
		15	15~24							22				
16		16~24	65	45	38	H+17	18	30						
20	20~30													
25	25~35													




Ordering Example

Part Number - W - H
 HGLTS20 - W20 - H40
 HGLNB12 - W12 - H35



Example



DH7	Unit Price				
	U-Shaped			T-Shaped	
	HGLTB	HGLTM	HGLTS	HGLNB	HGLNM
3					
4					
5					
6					
8					
10					
12					
13					
14					
15					
16					
20					
25					

Combination of these app. examples can be selected on our website.

For details of selections **P87**

*Enter the search keyword in the search box on e-Catalog. The search result will be shown in "Modular Assembler" area.

e-Catalog Search Keyword

