

NAKANISHI'S EXCLUSIVE TOOLS

Exclusive Tools of Ultrasonic Polisher "SHEENUS ZERO"



Special electroplated diamond files of Nakanishi's ultrasonic polisher "SHEENUS ZERO". Ideal for fine burr removal and rough finishing.

1 pc./pack Electroplated Diamond File

File Type	Diagram	Grit	Part No.
Flat taper		# 200	60101
		# 320	60102
		# 600	60103
Flat		# 200	60105
		# 320	60106
		# 600	60107
*60107 is thickness 0.8mm.			
Flat bent		# 200	60111
		# 320	60112
		# 600	60113
Column with the rounded edge		# 200	60151
		# 320	60152
		# 600	60153
Column with the rounded edge		# 200	60155
		# 320	60156
		# 600	60157
Round taper (cone-shaped)		# 200	60181
		# 320	60182
		# 600	60183
Triangular taper (Triangular pyramid)		# 200	60185
		# 320	60186
		# 600	60187
Oval taper		# 200	60191
		# 320	60192
		# 600	60193
Flat long		# 200	60115
		# 320	60116
		# 600	60117
Flat long taper		# 200	60231
		# 320	60232
		# 600	60233
Flat long taper		# 200	60235
		# 320	60236
		# 600	60237

2 pcs./pack Ceramic Fiber Grindstone (Total Length 50 mm)

Alumina fiber abrasive with the strength and the flexibility for rough or fine finishing.



Grindstone Type	Diagram	Grit	Color	W = 4 mm	W = 6 mm
Flat		# 120	Violet	60511	60516
		# 220	Brown	60512	60517
		# 400	Orange	60513	60518
		# 800	Blue	60514	60519
		# 1,200	Red	60515	60520
Round		# 220	Gray	60551	
		# 300	Magenta	60552	
		# 400	Orange	60553	
		# 600	Black	60554	
		# 800	Blue	60555	
		# 1,000	White	60556	
# 1,200	Red	60557			

5 pcs./pack Brass Lapping Tip (Total Length 40 mm)

Lapping tools for finishing using diamond or abrasive compounds.

Tip Shape	Diagram	Grain diameter	Part No.
Round		d=ø2.0 mm	60801
		d=ø3.0 mm	60802
Flat		d=ø3.3 mm	60803
		d=ø3.2 mm	60804
		d=ø3.0 mm	60805

Grain diameter	Part No.
d=ø2.0 mm	60801
d=ø3.0 mm	60802

60805

* Use after clamping in Special Tip Holder

2 pcs./pack Special Tip Holder • Choose by tip size and shape.

Holder Type	Diagram	Grain diameter	Part No.
Round		d=ø2.0 mm	60901
		d=ø3.0 mm	60902
		d=ø3.3 mm	60903
		d=ø3.2 mm	60904
Flat		t=0.8 mm	60921
		t=1.0 mm	60922
		t=2.0 mm	60923
		t=3.0 mm	60924
t=3.3 mm	60925		
Round		d=ø2.0 mm	60911
		d=ø3.0 mm	60912
		d=ø3.2 mm	60913

Used for Round Ceramic Fiber Grindstone. Best for soft materials.

Used for Flat Ceramic Fiber Grindstone. Best for both hard and soft materials.

Used for round tip (Brass Lapping Tip, Electroplated Diamond File: ● marked products on P.59). Best for hard materials.